




CONNECTOR HOUSINGS



✓ Active

[↓](#) **PRODUCT DRAWING**
English

[↓](#) **3D PDF**



TE CONNECTIVITY (TE)
110 UNSLD 2P PLUG ASSY
[Multilock Connector System](#)

2109366-2
TE Internal Number: 2109366-2

[Always EU RoHS/ELV Compliant](#)
Connector Style **Housing for male terminals**
Mating Tab Width **2.8 mm [.11 in]**
Number of Positions **2**
Pitch **8 mm [.315 in]**
Sealed **No**

Product Drawings

[110 UNSEALED 2P PLUG ASSY](#)
PDF
English

CAD Files

[3D PDF](#)
PDF
3D

[Customer View Model](#)
2D_DXF.ZIP
English

[Customer View Model](#)
3D_IGS.ZIP
English


[Customer View Model](#)
3D_STP.ZIP
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style	Housing for male terminals
Sealed	No
Hybrid Connector	No
Primary Locking Feature	On the terminal
Connector System	Wire-to-Wire

	Strain Relief	No
Configuration Features	Number of Positions	2
	Number of Rows	1
Electrical Characteristics	Operating Voltage (VDC)	12
Body Features	Body Material	PBT GF
	Cable Exit Angle	180°
	Color	Black
Contact Features	Mating Tab Width	2.8 mm [.11 in]
Mechanical Attachment	Terminal Position Assurance	Yes
	Mounting Feature	Yes
	Polarized	Yes
Housing Features	Pitch	8 mm [.315 in]
Dimensions	Width	35.5 mm [1.398 in]
	Height	12.6 mm [.496 in]
Usage Conditions	Operating Temperature Range	-40 – 80 °C [-40 – 176 °F]
Industry Standards	Degree of Protection	Other
	UL Flammability Rating	None
Other	Connector Position Assurance Capable	No
	Serviceable	Yes
Product Compliance	<div>Statement of Compliance PDF</div> <div>VIEW ALL PRODUCT COMPLIANCE</div>	





Relation Type



RELATIONSHIP

Contacts

Identifies Contacts compatible with a given Housing

See All Contacts



PRODUCT - CONTACTS

Connectors - Automotive, Truck, Bus, & Off-Road Terminals
AMP I Junior Power Timer, Timer Connector System

JUN-POW-TIM
KONTAKT - 964284-1

TE INTERNAL NUMBER: 964284-1

✓ Active

Always EU RoHS/ELV Compliant

Terminal Style **Receptacle/Socket**

Mating Tab Width **2.8 mm**

Mating Tab Thickness **.8 mm**

Terminal Transmits **0 – 24 A (Low Power)**

Sealed **No**



RELATIONSHIP

Contacts

Identifies Contacts compatible with a given Housing

See All Contacts



PRODUCT - CONTACTS

Connectors - Automotive, Truck, Bus, & Off-Road Terminals
AMP I Junior Power Timer, Timer Connector System

JUNIOR POWER TIMER
CONTACT - 964284-2

TE INTERNAL NUMBER: 964284-2

✓ Active

Always EU RoHS/ELV Compliant

Terminal Style **Receptacle/Socket**

Mating Tab Width **2.8 mm**

Mating Tab Thickness **.8 mm**

Terminal Transmits **0 – 24 A (Low Power)**

Sealed **No**

