



Home> Products > MICRO SWITCH™ Sealed and High Accuracy Switches > AT > Product Page

64AT34-3



Actual product appearance may vary.

AT Series Toggle Switch, 4 pole, 2 position, H58 terminal, Standard Lever

Features

- Gold or silver contacts
- Choice of sealed bushing
- Standard or pull to unlock toggle lever
- Short behind-panel depth
- Solder or quick connect termination
- 2,4, 6, or 8 SPDT precision basic switches
- 2 or 3 position, momentary or maintained action

Potential Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Description

Compact multipole 2, 4, 6,or 8 SPDT design. MICRO SWITCH™ precision basic switches conserve space and weight. Pull -to-Unlock Toggle Levers prevent accidental operation: the lever must be pulled approximately 2,3 mm [0.09 inches] to change the positions. Many locking configurations are available. Lever to bushing seals. Hermetic basic switches are available. AT qualified versions meet MILS-8805/98. Various levers and styles are available.

Supporting Documentation

- [Accessory: Lever Sleeve](#)
- [Accessory: Seals](#)
- [Accessory: Nuts](#)
- [Engineering Drawing](#)

| Product Specifications                |                                                                              |
|---------------------------------------|------------------------------------------------------------------------------|
| Circuitry/Operating action            | <div><div>Keyway Maintained</div><div>Opposite Keyway Maintained</div></div> |
| Product Type                          | MICRO SWITCH™ Toggle                                                         |
| Ampere/Voltage Range (Resistive Load) | 0.1 A to 1.0 A at 0.5 Vdc to 28 Vdc,0.1 A to 1.0 A at 0.5 Vac to 115 Vac     |
| Circuitry                             | 4PDT                                                                         |
| Action                                | 2 position                                                                   |
| Mounting                              | Bushing 15/32 in                                                             |
| Termination                           | H58                                                                          |
| Comment                               | FAA- PMA approved, contains 24K solid gold contacts                          |
| Availability                          | Global                                                                       |
| UNSPSC Code                           | 30211908                                                                     |
| UNSPSC Commodity                      | 30211908 Toggle switches                                                     |
| Series Name                           | AT                                                                           |

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (\*) to expand search

Specification Search