


Part Number : 743209010
Product Description : MicroCross DVI-I Digital/ Analog Visual Interface, PCB Receptacle, Panel Mount, Through Hole, Right-Angle, with Beveled Metal Pins, 0.76µm Gold (Au), Lead-Free, Screw Hole, 4-40 Thread, 29 Circuits
Series Number : 74320
Status : Not Recommended For New Design
Product Category : I/O Connectors

Documents and Resources

Drawings

743209010_sd.pdf

PK-74320-005-001.pdf

PK-74320-010-002.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-74320-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	I/O Connectors
Series	74320
Description	MicroCross DVI-I Digital/Analog Visual Interface, PCB Receptacle, Panel Mount, Through Hole, Right-Angle, with Beveled Metal Pins, 0.76µm Gold (Au), Lead-Free, Screw Hole, 4-40 Thread, 29 Circuits
Application	Wire-to-Board
Comments	DDWG (Digital Display Working Group) Standard
Component Type	Receptacle
Product Name	MicroCross DVI
Type	N/A
UPC	800754861878

Agency

UL	E29179

Electrical

Current - Maximum per Contact	3.0A

Downloaded from Arrow.com.

Grounding to Panel	Yes
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	40V AC (RMS)

Physical

Boot Color	N/A
Circuits (Loaded)	29
Circuits (maximum)	29
Color - Resin	Natural
Durability (mating cycles max)	100
Gender	Receptacle
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	6.714/g
Number of Rows	3
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PC Tail Length	2.34mm
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20° to +85°C
Termination Interface Style	Through Hole
Waterproof / Dustproof	No

Downloaded from Arrow.com.

Wire Size (AWG)	N/A

Solder Process Data

Lead-Free Process Capability	WAVE

Downloaded from Arrow.com.