molex



Part Number : 1727186121
Product Description : Mini-Fit TPA2/Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 24-22 AWG, 1.65-2.38mm Insulation Diameter, Reel
Series Number : 172718
Status : Active
Product Category : Crimp Terminals
Packaging Alternative : 1727186122 (Bag)

Documents and Resources

Drawings

1727186121_sd.pdf

PK-172718-0000-000.pdf

PK-172718-0001-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-172718-0000-001.pdf

PS-172718-0000-001.pdf

2131370000-PS-000.pdf

1727180001-TS-000.pdf

1727180002-TS-000.pdf

1727180003-TS-000.pdf

2131370001-TS-000.pdf

2131370002-TS-000.pdf

Tooling Specifications

ATS-2002180200-001.pdf

ATS-2002181200-001.pdf

ATS-639037000-001.pdf

Product Environment Compliance

Downloaded from Arrow.com.

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	172718
Description	Mini-Fit TPA2/Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 24-22 AWG, 1.65-2.38mm Insulation Diameter, Reel
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See product specification for current derating information; See Mini-Fit TPA2 housing series

Downloaded from Arrow.com.

	for 3D models.
Product Name	Mini-Fit Sigma,Mini-Fit TPA2
UPC	889056179416

Electrical

Current - Maximum per Contact	11.5A
Voltage - Maximum	600V AC/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.210/g
Packaging Type	Reel
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.65-2.38mm
Wire Size (AWG)	22, 24
Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Receptacle Housings	172708
Mini-Fit TPA2 and Mini-Fit Sigma Single Row Receptacle Housings	200453

Downloaded from Arrow.com.

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 22 AWG, Large and Small Insulation Grips	2002180200
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 24 AWG, Large and Small Insulation Grips	2002181200
Extraction Tool for Mini-Fit TPA2 Crimp Terminal, 24-16 AWG	638246210
FineAdjust Applicator for Mini-Fit TPA2 Crimp Terminals, 0.22mm^2, 0.25mm^2, 0.35 mm^2 and 24-22 AWG wires	639037000

Downloaded from Arrow.com.