



1 2 3 4 5 6 7



① PIN ASSIGNMENT

P1	P2
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
Shell	Shell

Electrical test:
 1. 100% short, open, miss wire test
 2. Conduct resistance: 2 Ohm max.
 3. Insulator resistance: 5Mohm min.
 4. Hi-Pot: 300V DC/10ms

NO.	NAME.	QTY	SPECIFICATION
⑨	PE Bag	1pcs	Clear Print black "MADE IN CHINA"+ "1PC"
⑧	Tie	1pcs	White tie
⑦	Outermold	NA	PVC 45P Beige(BG002)
⑥	Innermold	NA	LD-PE
⑤	Tube	2pcs	Heat shrink tube black OD:Ø1.5*L15mm
④	Screw	4pcs	Screw #4-40UNC D-E L=32.5mm Nickel plated Insulator color:Beige(BG002)
③	CONN	1pcs	DB 9Pin Female,Pin:G/F Shell-Nickel Insulator color:Blue solder type
②	CONN	1pcs	DB 9Pin male,Pin:G/F Shell-Nickel Insulator color:Blue solder type
①	Cable	1pcs	No UL 28AWG(7/0.12TC)*9C+D+AL/Mylar Jacket PVC,Beige(BG002) OD:5.0mm

RoHS compliant
Unit:mm

Scale	Free	Date	Name	Customer-No.
TOLERANCE		Drawn	05.04.2016	Amy
TOLERANCE		Approved	05.04.2016	Amy
				ASSMANN WSW-No. AK131-2
				Drawing-No. ASS 7603 CA rev01
DIM	TOL	① Update pin assignment	20.12.2018	Xavier
DIM	TOL	② Drawn	05.04.2016	Amy
Angle	TOL	Id.	Modification	Date



1 2 3 4 5 6 7