



**CONNECTORS**

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✓ Active

TE CONNECTIVITY (TE)

## ASSY, PLUG, 2P SEALED, 2.8 MCP

AMP MCP 2.8 , AMP MCP Connector System

1326455-1

TE Internal Number: 1326455-1

EU RoHS Compliant

EU ELV Compliant

**Connector Style** Housing for female terminals

**Mating Tab Width** 2.8 mm [.11 in]

**Connector System** Wire-to-Wire

**Number of Positions** 2

**Centerline (Pitch)** 6.5 mm [.256 in]

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

### DOCUMENTATION

Product Drawings

#### ASSEMBLY, PLUG, SEALED, 2 POSITION MCP 2.8

PDF

English

CAD Files

**3D PDF**

PDF

**3D**

#### Customer View Model

2D\_DXF.ZIP

English

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

---

Product Specifications

Product Specification

## Truck Lighting Connector System

PDF

English

Qualification Test Report

## Truck Lighting Connector System

PDF

English

---

Instruction Sheets

Instruction Sheet (U.S.)

## Truck Light Connector System

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Connector Style** Housing for female terminals

**Connector System** Wire-to-Wire

**Sealable** Yes

**Hybrid Connector** No

**Primary Locking Feature** On the terminal

**Strain Relief** Add By Accessory

---

### Configuration Features

**Number of Positions** 2

**Number of Rows** 1

---

### Electrical Characteristics

**Nominal Voltage Architecture (V)** 12, 24

**Operating Voltage (VDC)** 24

---

### Body Features

**Color** Black  
**Cable Exit Angle** 180°  
**Body Material** PA GF

---

#### Contact Features

**Mating Tab Width** 2.8 mm [.11 in]

---

#### Mechanical Attachment

**Mounting Feature** No  
**Terminal Position Assurance** Yes  
**Polarized** Yes

---

#### Housing Features

**Centerline (Pitch)** 6.5 mm [.256 in]

---

#### Dimensions

**Width** 22.9 mm [.9016 in]  
**Height** 22.8 mm [.8976 in]  
**Length** 31 mm [1.22 in]

---

#### Usage Conditions

**Operating Temperature Range** -40 – 85 °C [-40 – 185 °F]

---

#### Operation/Application

**Circuit Application** Signal

---

#### Industry Standards

**Degree of Protection** IP67  
**UL Flammability Rating** UL 94-HB

---

#### Packaging Features

**Packaging Method** Package  
**Packaging Quantity** 600

---

#### Other

**Connector Position Assurance Capable** No  
**Serviceable** Yes

---

## PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF

---

