



Home> Products > Detector > Photodarlington > Product Page

SDP8106-001



Actual product appearance may vary.

SDP Series Silicon PhotoDarlington,
Side-looking Plastic Package

Features

- Side-looking plastic package
- 50 ° (nominal) acceptance angle
- Mechanically and spectrally matched to SEP8506 and SEP8706 infrared emitting diodes

Description

The SDP8106 is an NPN silicon photodarlington molded in a side-looking black plastic package to minimize effect of visible ambient light. The chip is positioned to accept radiation through a plastic lens from the side of the package.

Supporting Documentation

- Dimensions
- Schematic
- Performance Charts
- Engineering Drawing

Product Specifications	
Series Name	Photodarlington
Product Type	IR Component
Angular Response (Degree)	50
Light Current Minimum	1.0 mA
Package Style	Side-Looking
Package Components	Plastic
Package Color	Black
Rise and Fall Time	75 µs
Power Dissipation	100 mW
Operating Temperature Range	-40 °C to 85 °C [-40 °F to 185 °F]
Dark Current	250 nA
Collector-Emitter Breakdown Voltage	15 V
Emitter-Collector Breakdown Voltage	5 V
Collector-Emitter Saturation Voltage	1.1 V
Comment	The radiation source is a IRED with a peak wavelength of 935 nm.
Availability	Global

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search