

Null Modem Serial DB9 Serial Cable (DB9 to DB25 F/M), 6 ft. (1.83 m)

MODEL NUMBER: P456-006



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold-plated connectors provide superior conductivity
- Null modem cables connect two serial devices that require a null modem configuration

System Requirements

- Two serial devices (one with a DB25 Male connector and the Other with a DB9 Female connector) requiring a null modem (cross-wired) configuration.

Package Includes

- 6-ft. (1.83 m) Null Modem Gold Cable DB9F to DB25M

Description

Null modem cables and adapters connect two serial devices that require a null modem (cross-wired) configuration. This 6-ft. (1.83 m) cable has a DB9 female connector on one end and a DB25 male connector on the other. Superior molded cables with foil-shielding offer maximum EMI/RFI protection. Gold-plated connectors and contacts provide superior conductivity.

Features

- DB9 female to DB25 male
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold-plated connectors provide superior conductivity

Specifications

| OVERVIEW | |
|----------------------|--------------|
| UPC Code | 037332013354 |
| Technology | Serial |
| CONNECTIONS | |
| Side A - Connector 1 | DB9 (FEMALE) |
| Side B - Connector 1 | DB25 (MALE) |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 6 |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 8.50 x 6.90 x 0.50 |
| Shipping Dimensions (hwd / cm) | 21.59 x 17.53 x 1.27 |
| Shipping Weight (lbs.) | 0.37 |
| Shipping Weight (kg) | 0.17 |
| Unit Dimensions (hwd / in.) | 8.500 x 6.900 x 0.500 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.