




NOTES:

- 1. RESISTANCE @ 25°C : 10KΩ ± 1%
- 2. BETA VALUE (0/50°C) : 3892K ± 1%
- 3. OPERATING TEMPERATURE RANGE : -40°C TO +250°C.
- 4. THERMAL TIME CONSTANT : 15SEC IN WATER
- 5. VOLTAGE BREAKDOWN STRENGTH : 1500V AC FOR 3SEC.
- 6. INSULATION RESISTANCE : A MINIMUM OF 100MΩ @ 500VOLTS DC.
- 7. DISSIPATION FACTOR : 1mW/°C.
- 8. LASER MARKING "MOLEX-DATE CODE(MM/YY)" & "XXK(R25-value) XXXX(B-value)"

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex							
	mm		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
ANGULAR TOL ± °															
4 PLACES ±															
DIVISIONAL SYMBOLS	3 PLACES ±		EC NO: 727818		DRWN: NANDAK 2022/11/09			GLASS NTC PROBE A -10K±1%,B3892,L100							
	3 PLACES ±		CHK'D: RBBHASKAR 2022/11/15												
	2 PLACES ±		APPR: RBBHASKAR 2022/11/15												
	1 PLACE ±		INITIAL REVISION:		DOCUMENT NUMBER						DOC TYPE	DOC PART	REVISION		
	0 PLACES ±		DRWN: RAVIKM 2022/01/28		2185353607						PSD	000	A2		
		APPR: RBBHASKAR 2022/02/18													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		218535		2185353607		GENERAL MARKET		1 OF 2	

