

10A, 100V - 200V Ultra Fast Surface Mount Rectifier

FEATURES

- Planar technology
- Low power loss, high efficiency
- Ideal for automated placement
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free



APPLICATIONS

- High frequency switching
- DC/DC
- Snubber

MECHANICAL DATA

- Case: ThinDPAK
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 0.194g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I _F	10	A
V _{RRM}	100 - 200	V
I _{FSM}	130	A
T _{J MAX}	175	°C
Package	ThinDPAK	
Configuration	Common cathode	


ThinDPAK®

ThinDPAK


ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)

PARAMETER	SYMBOL	PUAD10BC	PUAD10DC	UNIT
Marking code on the device		UAD10BC	UAD10DC	
Repetitive peak reverse voltage	V _{RRM}	100	200	V
Reverse voltage, total rms value	V _{R(RMS)}	70	140	V
Forward current per device	I _F	10		A
Surge peak forward current single half sine-wave superimposed on rated load per diode	t = 8.3ms	I _{FSM}	130	A
	t = 1.0ms		270	
Junction temperature	T _J	-55 to +175		°C
Storage temperature	T _{STG}	-55 to +175		°C

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\Theta JL}$	3.5	°C/W
Junction-to-ambient thermal resistance	$R_{\Theta JA}$	11.8	°C/W
Junction-to-case thermal resistance	$R_{\Theta JC}$	2.0	°C/W

Thermal Performance Note: Mounted on heat sink with 2" x 3" x 0.25" Al-Plate

ELECTRICAL SPECIFICATIONS (T_A = 25°C unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	$I_F = 2.5A, T_J = 25^{\circ}C$	V_F	0.81	-	V
	$I_F = 2.5A, T_J = 125^{\circ}C$		0.66	-	V
	$I_F = 5.0A, T_J = 25^{\circ}C$		0.88	0.95	V
	$I_F = 5.0A, T_J = 125^{\circ}C$		0.74	-	V
Reverse current @ rated V _R per diode ⁽²⁾	$T_J = 25^{\circ}C$	I_R	-	2	µA
	$T_J = 125^{\circ}C$		2	-	µA
Junction capacitance per diode	1MHz, $V_R = 4.0V$	C_J	74	-	pF
Reverse recovery time	$I_F = 0.5A, I_R = 1.0A, I_{rr} = 0.25A$	t_{rr}	-	25	ns
	$I_F = 1.0A, dI/dt = 50A/\mu s, V_R = 30V$		24	-	
Reverse recovery current	$I_F = 5.0A, dI/dt = 200A/\mu s, V_R = 100V$	I_{RM}	2.9	-	A
Reverse recovery charge		Q_{rr}	41	-	nC
Reverse recovery time		t_{rr}	20	-	ns

Notes:

1. Pulse test with PW = 0.3ms
2. Pulse test with PW = 30ms

ORDERING INFORMATION

ORDERING CODE ⁽¹⁾	PACKAGE	PACKING
PUAD10xC	ThinDPAK	4,500 / Tape & Reel

Notes:

1. "x" defines voltage from 100V(PUAD10BC) to 200V(PUAD10DC)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics










Fig.5 Typical Transient Thermal Impedance




PACKAGE OUTLINE DIMENSIONS
ThinDPAK


DETAIL A, ROTATED -90°
(SCALE 4:1)



**SUGGESTED PAD
LAYOUT**



MARKING DIAGRAM

YWW = DATE CODE
F = FACTORY CODE
P/N = MARKING CODE

NOTES: UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
3. PACKAGE OUTLINE REFERENCE: JEDEC TO-252, VARIATION AE, ISSUE F.
4. MOLDED PLASTIC BODY DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSION, OR GATE BURRS.
5. DWG NO. REF: HQ2SD07-TDPAK-065 REV A.

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.