

HAN^Ø Port is an interface that provides a convenient and environmentally protected method of accessing the network ports.

Features & Benefits:

- HAN[®] Port typically mounts on the outside of an enclosure.
- HAN[®] Port maintains the NEMA 12/4 integrity of control systems.
- HAN[®] Port provides safety and convenience to programmers and trouble-shooters.
- HAN[®] Port protects control devices from unwanted substances, such as dust, dirt, oil, chemicals, etc.
- HAN[®] Port is UL recognized (UR), CSA, and CE certified.
- HAN[®] Port is available in 3 different termination styles, i.e. PC boards with terminal blocks, complete cable extension solutions, and bulk-head (pass-thru) connectors.













HAN[®] Port is the solution to meet new electrical safety requirements specified by the National Fire Protection Agency (70E Standard). The new standard, which is currently in draft form, requires employees who are within four feet of live (exposed) 50 to 600 volts to wear the following protective clothing:

- Safety Glasses
- Face Shield
- Flame Resistant Clothing
- Hand and Arm Protection (Gloves)

Given the stringent requirements, HAN[®] Port allows users to maintain convenience, safety, and efficiency.









HAN⁰ Port



Description	Part Number Panel Cutout	Drawing
 HAN⁰ Prog Port RJ45	73 55 040 0901  (Dimensions are in inches)	 CAT. 5 RJ-45 INTERFACE 
 HAN⁰ Prog Port RJ45 120VAC	73 55 040 0914  (Dimensions are in inches)	 120VAC OUTLET (5A MAX) (CODE: R6) RJ45 CAT5 BULKHEAD ETHERNET CONNECTOR (CODE: R2) REAR VIEW 
 HAN⁰ Prog Port RJ45 120VAC 3A	73 55 040 0915  (Dimensions are in inches)	 120VAC OUTLET WITH 3A BREAKER (CODE: R6) RJ45 CAT5 BULKHEAD ETHERNET CONNECTOR (CODE: R2) REAR VIEW 
 HAN⁰ Prog Port DB9F/M RJ45	73 55 040 0903  (Dimensions are in inches)	 DB9 F/M BULKHEAD CONNECTOR INTERFACE (CODE: Q7) RJ45 F/F BULKHEAD CONNECTOR INTERFACE (CODE: Q17) 









HAN⁰ Port



Description	Part Number Panel Cutout	Drawing
 HAN⁰ Prog Port DB9M	73 55 040 0905  (Dimensions are in inches)	
 HAN⁰ Prog Port DB9F Terminal Blk	73 55 040 0902  (Dimensions are in inches)	
 HAN⁰ Prog Port DB9F/M	73 55 040 0904  (Dimensions are in inches)	
 HAN⁰ Prog Port DB9M RJ45	73 55 040 0907  (Dimensions are in inches)	









HAN⁰ Port



Description	Part Number Panel Cutout	Drawing
 HAN⁰ Prog Port DB9M 120VAC	73 55 040 0908  (Dimensions are in inches)	
 HAN⁰ Prog Port DB9F Terminal Blk 120VAC	73 55 040 0913  (Dimensions are in inches)	
 HAN⁰ Prog Port DB9M 120VAC 3A	73 55 040 0923  (Dimensions are in inches)	
 HAN⁰ Prog Port DB9F/M RJ45 120VAC	73 55 040 0912  (Dimensions are in inches)	









HAN^o Port



Description	Part Number Panel Cutout	Drawing
 HAN^o Prog Port DB9M RJ45 120VAC	73 55 040 0921  (Dimensions are in inches)	 120VAC OUTLETA (MAX) (CODE:R0) COMPUTER SERIAL PORT CABLE INTERFACE (CODE:P1) ETHERNET CAT.5 BULK-HEAD CONNECTOR INTERFACE (CODE:R2) 10 FOOT CABLE ASSEMBLY DB9 FEMALE
 HAN^o Prog Port DB9F Terminal Blk 120VAC 3A	73 55 040 0916  (Dimensions are in inches)	 120VAC OUTLETA 3A BREAKER (CODE:R0) CODE:R0/120VAC OUTLET INTERFACE (CODE:R1) WIRE ENTRY CODE:P1 INTERFACE FRONT FACE SIDE BACK FACE
 HAN^o Prog Port DB9M RJ45 120VAC 3A	73 55 040 0920  (Dimensions are in inches)	 120VAC OUTLETA WITH 3A BREAKER (CODE:R0) COMPUTER SERIAL PORT CABLE INTERFACE (CODE:P1) ETHERNET CAT.5 BULK-HEAD CONNECTOR 10 FOOT CABLE ASSEMBLY DB9 FEMALE
 HAN^o Prog Port 2x6 Pin Mini Din	73 55 040 0906  (Dimensions are in inches)	 5 PIN MINIDIN KEYBOARD/MOUSE CONNECTORS (CODE:P3P5) 6 FOOT CABLE ASSEMBLY CABLE PINOUT (WALL PLUG MOUNTS IN INTERFACE HOUSING) FEMALE MALE









HAN^o Port



Description	Part Number Panel Cutout	Drawing
 HAN^o Prog Port 2x6 Pin Mini Din RJ45	73 55 040 0910  (Dimensions are in inches)	 6 PIN MINIDIN MALE
 HAN^o Prog Port 2x6 Pin Mini Din 120VAC	73 55 040 0911  (Dimensions are in inches)	 6 PIN MINIDIN MALE
 HAN^o Prog Port 2x6 Pin Mini Din 120VAC 3A	73 55 040 0918  (Dimensions are in inches)	 6 PIN MINIDIN MALE
 HAN^o Prog Port 2x6 Pin Mini Din DB9M 120VAC	73 55 040 0922  (Dimensions are in inches)	 6 PIN MINIDIN MALE



HAN^o Port



Description	Part Number Panel Cutout	Drawing
 HAN^o Prog Port 2x6 Pin Mini Din RJ45 120VAC	73 55 040 0917  (Dimensions are in inches)	
 HAN^o Prog Port DB25F	73 55 040 0909  (Dimensions are in inches)	
 HAN^o Prog Port DB25F 120VAC	73 55 040 0919  (Dimensions are in inches)	
 HAN^o Prog Port (48B) Without 3A Breaker	73 55 040 0924  (Dimensions are in inches)	

HAN⁰ Port



Description	Part Number Panel Cutout	Drawing
 HAN⁰ Prog Port (48B) With 3A Breaker	73 55 040 0925  (Dimensions are in inches)	 PS/2 KEYBOARD/MOUSE CABLE INTERFACE (CODE:P3P5) COMPUTER SERIAL PORT CABLE INTERFACE (CODE:P1) VGA MONITOR CABLE INTERFADE (CODE:PB) COMPUTER PARALLEL PORT CABLE INTERFACE (CODE:P2) ETHERNET CAT.5 BULKHEAD CONNECTOR INTERFACE (CODE:R2) 120VAC OUTLET WITH 3A BREAKER (CODE:R3)

Part Number	Description	Page
73 55 040 0901	HAN [®] Prog Port RJ45	2
73 55 040 0902	HAN [®] Prog Port DB9F Terminal Blk	3
73 55 040 0903	HAN [®] Prog Port DB9F/M RJ45	2
73 55 040 0904	HAN [®] Prog Port DB9F/M	3
73 55 040 0905	HAN [®] Prog Port DB9M	3
73 55 040 0906	HAN [®] Prog Port 2x6pin mini Din	5
73 55 040 0907	HAN [®] Prog Port DB9M RJ45	3
73 55 040 0908	HAN [®] Prog Port DB9M 120VAC	4
73 55 040 0909	HAN [®] Prog Port DB25F	7
73 55 040 0910	HAN [®] Prog Port 2x6pin mini Din RJ45	6
73 55 040 0911	HAN [®] Prog Port 2x6 pin mini Din 120VAC	6
73 55 040 0912	HAN [®] Prog Port DB9F/M RJ45 120VAC	4
73 55 040 0913	HAN [®] Prog Port DB9F Terminal Blk 120 VAC	4
73 55 040 0914	HAN [®] Prog Port RJ45 120VAC	2
73 55 040 0915	HAN [®] Prog Port RJ45 120VAC 3A	2
73 55 040 0916	HAN [®] Prog Port DB9F Term Blk 120VAC 3A	5
73 55 040 0917	HAN [®] Prog Port 2x6pin mini Din RJ45 120VAC	7
73 55 040 0918	HAN [®] Prog Port 2x6pin mini Din 120VAC 3A	6
73 55 040 0919	HAN [®] Prog Port DB25F 120VAC	7
73 55 040 0920	HAN [®] Prog Port DB9M RJ45 120VAC 3A	5
73 55 040 0921	HAN [®] Prog Port DB9M RJ45 120VAC	5
73 55 040 0922	HAN [®] Prog Port 2x6pin mini Din DB9M 120VAC	6
73 55 040 0923	HAN [®] Prog Port DB9M 120VAC 3A	4
73 55 040 0924	HAN [®] Prog Port (48B)	7
73 55 040 0925	HAN [®] Prog Port (48B)	8



HARTING, Inc. of North America
1370 Bowes Road
Elgin, IL 60123
Tel (847) 741-1500
Fax (847) 741-8257
www.HARTING.com
Email: moreinfo@harting-usa.com