

MLF1005VR15JT000

Product Status	Production
Applications	Commercial Grade
Feature	No Directivity
	Multilayer
	Shield
Series Type	MLF
Brand	TDK
Environmental Compliance	 RoHS  REACH  Halogen Free  Lead Free



Size	
Length(L)	1.00mm ± 0.05 mm
Width(W)	0.50mm ± 0.05 mm
Thickness Height	0.50mm ± 0.05 mm
Recommended Land Pattern (A)	0.50mm Nom.
Recommended Land Pattern (B)	0.40mm Nom.
Recommended Land Pattern (C)	0.50mm Nom.

Electrical Characteristics	
Inductance	150nH $\pm 5\%$ at 25MHz
Rated Current (L Change) [Typ.]	
Rated Current (L Change) [Max.]	180mA
Rated Current (Temperature Rise) [Typ.]	
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	390m Ω
DC Resistance [Max.]	630m Ω
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	350MHz
Self Resonant Frequency [Typ.]	650MHz
Q [Min.]	15 at 25MHz
Q [Typ.]	30 at 25MHz

Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel]

! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.





! All specifications are subject to change without notice.

Package Quantity	10000pcs
Weight	0.0012g

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

MLF1005VR15JT000

Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.


! All specifications are subject to change without notice.

Associated Images

Shapes and Dimensions



Land Pattern (Terminal Connection)



Dimensions in mm

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.