



Automotive-grade low voltage PNP power transistor



SC07710_TAB



Features

- AEC-Q101 qualified 
- Surface-mounting TO-252 power package in tape and reel
- Complementary to the NPN type [MJD31CT4-A](#)

Application

- General purpose linear and switching equipment

Description

The device is manufactured in planar technology with a “base island” layout. The resulting transistor shows exceptional high gain performance coupled with very low saturation voltage.

Product status link

[MJD32CT4-A](#)

Product summary

Order code	MJD32CT4-A
Marking	MJD32C
Package	DPAK
Packing	Tape and reel

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-base voltage ($I_E = 0$ A)	-100	V
V_{CEO}	Collector-emitter voltage ($I_B = 0$ A)	-100	V
V_{EBO}	Collector-base voltage ($I_C = 0$ A)	-5	V
I_C	Collector current	-3	A
I_{CM}	Collector peak current	-5	A
I_B	Base current	-1	A
P_{TOT}	Total power dissipation at $T_C = 25$ °C	15	W
T_{stg}	Storage temperature range	-65 to 150	°C
T_J	Operating junction temperature range		°C

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJC}	Thermal resistance, junction-to-case	8.3	°C/W
$R_{thJA}^{(1)}$	Thermal resistance, junction-to-ambient	50	°C/W

1. When mounted on a standard 1 inch² area of FR-4 PCB with 2-oz copper.

2 Electrical characteristics

$T_J = 25^\circ\text{C}$ unless otherwise specified.

Table 3. Electrical characteristics

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{CES}	Collector cut-off current	$V_{CE} = -100\text{ V}, V_{BE} = 0\text{ V}$		-	-20	μA
I_{CEO}	Collector cut-off current	$V_{CB} = -60\text{ V}, I_B = 0\text{ A}$		-	-50	μA
I_{EBO}	Emitter cut-off current	$V_{EB} = -5\text{ V}, I_C = 0\text{ A}$		-	-0.1	mA
$V_{CEO(sus)}^{(1)}$	Collector-emitter sustaining voltage	$I_C = -30\text{ mA}, I_B = 0\text{ A}$	-100	-		V
$V_{CE(sat)}^{(1)}$	Collector-emitter saturation voltage	$I_C = -3\text{ A}, I_B = -375\text{ mA}$		-	-1.2	V
$V_{BE(on)}^{(1)}$	Base-emitter on voltage	$I_C = -3\text{ A}, V_{CE} = -4\text{ V}$		-	-1.8	V
h_{FE}	DC current gain	$I_C = -1\text{ A}, V_{CE} = -4\text{ V}$	25	-		
		$I_C = -3\text{ A}, V_{CE} = -4\text{ V}$	10	-	50	

1. Pulse test: pulse duration $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.

2.1 Electrical characteristics (curves)

Figure 1. Safe operating area




Figure 2. Derating curve




Figure 3. DC current gain ($V_{CE} = 2$ V)




Figure 4. DC current gain ($V_{CE} = 4$ V)




Figure 5. Collector-emitter saturation voltage




Figure 6. Base-emitter saturation voltage




Figure 7. Base-emitter on voltage




Figure 8. Resistive load switching time (on)





Figure 9. Resistive load switching time (off)




3 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

3.1 DPAK (TO-252) package information

Figure 10. DPAK (TO-252) type A package outline



0068772_A_36

Table 4. DPAK (TO-252) type A mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	2.20		2.40
A1	0.90		1.10
A2	0.03		0.23
b	0.64		0.90
b4	5.20		5.40
c	0.45		0.60
c2	0.48		0.60
D	6.00		6.20
D1	4.95	5.10	5.25
E	6.40		6.60
E1	4.60	4.70	4.80
e	2.159	2.286	2.413
e1	4.445	4.572	4.699
H	9.35		10.10
L	1.00		1.50
(L1)	2.60	2.80	3.00
L2	0.65	0.80	0.95
L4	0.60		1.00
R		0.20	
V2	0°		8°


Technical drawing of a mechanical part. The drawing shows a top view and a side view. The top view is a rectangle with a width of 6.3 and a height of 6.5. The side view is a rectangle with a width of 11.2 and a height of 1.8 MIN. The part has two rectangular features on the top surface, each with a width of 1.5 and a height of 2.9. The distance between the centers of these two features is 4.572. The part is shown with section lines (hatching) indicating the material. The drawing includes dimension lines and arrows indicating the measurement of the features.

2) The device must be positioned within $\oplus 0.05 \text{ A B}$


page 8/13

3.2 DPAK (TO-252) packing information

Figure 12. DPAK (TO-252) tape outline



AM08852v1

Figure 13. DPAK (TO-252) reel outline


AM06038v1

Table 5. DPAK (TO-252) tape and reel mechanical data

Tape			Reel		
Dim.	mm		Dim.	mm	
	Min.	Max.		Min.	Max.
A0	6.8	7	A		330
B0	10.4	10.6	B	1.5	
B1		12.1	C	12.8	13.2
D	1.5	1.6	D	20.2	
D1	1.5		G	16.4	18.4
E	1.65	1.85	N	50	
F	7.4	7.6	T		22.4
K0	2.55	2.75			
P0	3.9	4.1	Base qty.		2500
P1	7.9	8.1	Bulk qty.		2500
P2	1.9	2.1			
R	40				
T	0.25	0.35			
W	15.7	16.3			

Revision history

Table 6. Document revision history

Date	Revision	Changes
01-Jun-2007	1	First release
09-Nov-2009	2	Updated package mechanical data.
14-Jan-2010	3	Modified <i>Table 3</i> on <i>page 2</i> .
19-Jun-2012	4	Modified: mechanical data updated
24-Jan-2018	5	Modified title. Modified features on cover page. Updated <i>Section 4: Package information</i> . Minor text changes.
05-Jul-2024	6	Updated <i>Features</i> . on cover page. Removed section test circuits. Updated <i>Section 3.1: DPAK (TO-252) package information</i> . Minor text changes.
16-Jun-2025	7	Updated Table 3. Electrical characteristics . Minor text changes.



Contents

1	Electrical ratings	2
2	Electrical characteristics	3
2.1	Electrical characteristics (curves)	4
3	Package information	6
3.1	DPAK (TO-252) package information	6
3.2	DPAK (TO-252) packing information	9
	Revision history	11

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved