






PRODUCT NUMBER	PITCH
YK321xx0x0JOG	7.62mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



SECTION P-P



MATERIALS & ELECTRICAL

- RATED VOLTAGE & CURRENT: 300V, 15 A
 WITHSTAND VOLTAGE: AC 2000 V/Min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 5.2 Lb-In
 WIRE RANGE: 22 - 14 AWG
 1) HOUSING: THERMOPLASTIC, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, #5-40

Safety Approval: us

PART NO.: YK 321xx 0 x 0 JOG

DIMENSION

Dim A	N×7.62±0.86
Dim B	(N-1)×7.62

N=Number of poles

Poles	Tolerance
2p-4p	±0.20
5p-21p	±0.30
22p-30p	±0.50

- No. of poles
 02 2 poles
 03 3 poles

 30 30 poles

Plated		
Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code		surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified	title TERMINAL BLOCK
				angles 	BARRIER TYPE
				X°±1'	scale
				dr EVAN LU 061014	dwg no
				enr EVAN LU 061014	sheet 1 of 1
				chr HANKE FENG 061014	size A4
				appd SHI JUN 061014	YK321xx0x0JOG
					type CUSTOMER Drawing
sheet index	revision sheet	A	1		