

Terminal Part Number: 02962447

Surface Plating: UNPLATED

Material Thickness [mm]: 0,46

Cross Section [mm²]: 2,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 1005

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 2,45 - 2,70

Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 2,00		2,58	200	1,70	0,05	3,30	0,10	3,00	0,10	4,10	0,10

Cable type code legend:

1005:



Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, PVDF, XLPE

Insul. Wall Designator: THIN



Terminal Part Number: 02962447

Surface Plating: UNPLATED

Material Thickness [mm]: 0,46

Cross Section [mm²]: 1,00 | 2,00

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable Type codes: 1007

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 2,45 - 3,10

Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1007 1,00		2,58	120	1,65	0,05	3,30	0,10	3,00	0,10	4,10	0,10
1007 2,00		2,98	200	1,70	0,05	3,30	0,10	3,10	0,10	4,10	0,10

Cable type code legend:

1007:


Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, XLPA/PVDF, XLPE

Insul. Wall Designator: REGULAR



Terminal Part Number: 02962447
Surface Plating: UNPLATED
Material Thickness [mm]: 0,46
Cross Section [mm²]: 2,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*



Cable Type codes: 1007
Crimp Process: (V) SOLDER - VARIAC - CORE IS BARE COPPER OR TINNED
Insulation Range Φ[mm]: 2,85 - 3,10
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1007 2,00		2,98	200	1,70	0,05	3,30	0,10	3,10	0,10	4,10	0,10

Cable type code legend:

1007:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPA/PVDF, XLPE
Insul. Wall Designator: REGULAR



Terminal Part Number: 02962447

Surface Plating: UNPLATED

Material Thickness [mm]: 0,46

Cross Section [mm²]: 0,80

Cable Type codes: 1007 + 7002

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Seal(s): NONE

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1007 0,80 + 7002 0,80		2,33 + 2,03	90	1,65	0,05	3,30	0,10	3,40	0,10	3,80	0,10

Cable type code legend:

1007:

Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, XLPA/PVDF, XLPE

Insul. Wall Designator: REGULAR

7002:



Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: SN

Insul. Material: PVC, XLPE

Insul. Wall Designator: THIN



Terminal Part Number: 02962447
Surface Plating: UNPLATED
Material Thickness [mm]: 0,46
Cross Section [mm²]: 1,00 | 2,00

This document is non-contractual
and for information only.

For more information, please
consult your local sales office



Cable Type codes: 1009
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,90 - 3,95
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1009 1,00		3,17	120	1,65	0,05	3,30	0,10	3,20	0,10	4,40	0,10
1009 2,00		3,73	200	1,70	0,05	3,30	0,10	3,30	0,10	4,50	0,10

Cable type code legend:

1009:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPE
Insul. Wall Designator: SPECIAL



Terminal Part Number: 02962447
Surface Plating: UNPLATED
Material Thickness [mm]: 0,46
Cross Section [mm²]: 1,00

*This document is non-contractual
and for information only.*



*For more information, please
consult your local sales office*

Cable Type codes: 1094
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,90 - 3,15
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1094 1,00		3,03	120	1,65	0,05	3,30	0,10	3,20	0,10	4,40	0,10

Cable type code legend:

1094:
Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPE
Insul. Wall Designator: HEAVY DUTY



Crimp Information Sheet

DELPHI

Terminal Part Number: 02962447
Surface Plating: UNPLATED
Material Thickness [mm]: 0,46
Cross Section [mm²]: 1,00 | 1,50 | 2,50

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2010
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ [mm]: 1,80 - 3,00
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 1,00		1,95	160	1,75	0,05	2,80	0,10	3,00	0,10	3,70	0,10
2010 1,50		2,20	200	1,85	0,05	2,85	0,10	3,10	0,10	3,70	0,10
2010 2,50		2,80	250	2,05	0,05	2,85	0,10	3,40	0,10	3,75	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR
(AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE,
XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Terminal Part Number: 02962447

Surface Plating: UNPLATED

Material Thickness [mm]: 0,46

Cross Section [mm²]: 0,80 | 1,00

Cable Type codes: 7002 + 1007

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Seal(s): NONE

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
7002 0,80 + 1007 1,00		2,03 + 2,58	90	1,75	0,05	3,35	0,10	3,60	0,10	3,80	0,10

Cable type code legend:

7002:

Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: SN

Insul. Material: PVC, XLPE

Insul. Wall Designator: THIN

1007:



Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, XLPA/PVDF, XLPE

Insul. Wall Designator: REGULAR



Terminal Part Number: 02962447
Surface Plating: UNPLATED
Material Thickness [mm]: 0,46
Cross Section [mm²]: 1,50

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable Type codes: 8000
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,20 - 2,40
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
8000 1,50		2,30	160	1,65	0,05	3,30	0,10	3,00	0,10	4,00	0,10

Cable type code legend:

8000:

Industry Designator: N/G
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: SYNTHRESIN
Insul. Wall Designator: THIN

