


REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	NEW PROPOSAL	JUL19/22	KELVIN




FRONT VIEW



SIDE VIEW



BACK VIEW



RECOMMENDED P.C.B LAYOUT
(TOLERANCE: ±0.05[±.002])
(PCB THICKNESS: 1.60 [.063])
(COMPONENT SIDE OF PC BOARD)

NOTES:

1. MATERIALS:
   CONTACTS: PHOSPHOR BRONZE, 0.35MM THICKNESS,
   PLATING: 6μ "[0.152 MICRONS] MIN. GOLD PLATING
   30μ "[0.762 MICRONS] MIN. NICKEL OVERALL.
   80μ "[2.032 MICRONS] MIN. MATTE TIN PLATING ON SOLDER TAILS.
   HOUSING: ENGINEERING THERMOPLASTIC, FLAMMABILITY RATING UL 94V-0
   COLOR - BLACK.
   SHIELD: BRASS WITH NICKEL PLATING


2. MECHANICAL:
   MATING FORCE: 5.0 LBS MAXIMUM

3. ELECTRICAL:
   CONTACT RESISTANCE: 20 MILLIOHMS MAXIMUM
   INSULATION RESISTANCE: 500 MEGOHMS MINIMUM
   CUTTENT RATING: 1.5 AMPS
   VOLTAGE RATING: 125 VOLTS AC

4. ENVIRONMENTAL:
   STORAGE TEMPERATURE: -40°C TO +85°C

5. RECOMMENDED SOLDERING TEMPERATURE:
   WAVE SOLDERING PEAKED AT 235°C FOR 5 SECONDS.

AMPHENOL PART NUMBER: RJE74-188-6110



RECOMMENDED PANEL CUTOUT

UNLESS SPECIFIED OTHERWISE	DRAWN RONNIE.C	JUL19/22	Amphenol Canada Corp. Commercial Products
PRIMARY UNITS MILLIMETERS	CHECKED KELVIN.T	JUL19/22	
SECONDARY INCHES	M.E. APP'D		SINGLE PORT, VERTICAL MODULAR JACK, 8 POSITION, 8 CONTACTS, SHIELDED –RoHS COMPLIANT
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APP'D		DWG NO. P–RJE74–188–6110 REV A
1 DECIMAL PLACE ±0.35	ENG. REL. NO.		
2 DECIMAL PLACES ±0.25	REF.		
3 DECIMAL PLACES ±0.15	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	CODE ID NO. 03554 | DWG SIZE X | SCALE N/A | SHEET 1 OF 1
ANGULAR DEGREES ±2.0°			

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Downloaded from Arrow.com.