

MOSFET - Power, N-Channel, SUPERFET® III, FAST

650 V, 67 mΩ, 40 A

NTH4L067N65S3H

Description

SUPERFET III MOSFET is onsemi's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provides superior switching performance, and withstand extreme dv/dt rate.

Consequently, SUPERFET III MOSFET FAST series is very suitable for the various power systems for miniaturization and higher efficiency.



Features

- 700 V @ $T_J = 150^\circ\text{C}$
- Typ. $R_{DS(on)} = 55 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ. $Q_g = 80 \text{ nC}$)
- Low Effective Output Capacitance (Typ. $C_{oss(\text{eff.})} = 691 \text{ pF}$)
- 100% Avalanche Tested
- These Devices are Pb-Free and are RoHS Compliant


Applications

- Telecom / Server Power Supplies
- Industrial Power Supplies
- UPS / Solar

V_{DSS}	$R_{DS(\text{ON}) \text{ MAX}}$	$I_D \text{ MAX}$
650 V	67 mΩ @ 10 V	40 A



MARKING DIAGRAM



A	= Assembly Site Code
YWW	= Data Code (Year & Week)
ZZ	= Assembly Lot Code
T067N65S3H	= Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

NTH4L067N65S3H

ABSOLUTE MAXIMUM RATINGS (T_C = 25°C, Unless otherwise noted)

Symbol	Parameter		Value	Unit
V _{DSS}	Drain to Source Voltage		650	V
V _{GSS}	Gate to Source Voltage	– DC	±30	V
		– AC (f > 1 Hz)	±30	
I _D	Drain Current	– Continuous (T _C = 25°C)	40	A
		– Continuous (T _C = 100°C)	25	
I _{DM}	Drain Current	– Pulsed (Note 1)	112	A
E _{AS}	Single Pulsed Avalanche Energy (Note 2)		422	mJ
I _{AS}	Avalanche Current (Note 2)		6.5	A
E _{AR}	Repetitive Avalanche Energy (Note 1)		2.66	mJ
dv/dt	MOSFET dv/dt		100	V/ns
	Peak Diode Recovery dv/dt (Note 3)		20	
P _D	Power Dissipation	(T _C = 25°C)	266	W
		– Derate Above 25°C	2.13	W/°C
T _J , T _{STG}	Operating and Storage Temperature Range		–55 to +150	°C
T _L	Maximum Lead Temperature for Soldering, 1/8" from Case for 5 seconds		260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Repetitive rating: pulse width limited by maximum junction temperature.
2. I_{AS} = 6.5 A, R_G = 25 Ω, starting T_J = 25°C.
3. I_{SD} ≤ 20 A, di/dt ≤ 200 A/μs, V_{DD} ≤ 400 V, starting T_J = 25°C.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
R _{θJC}	Thermal Resistance, Junction to Case, Max.	0.47	°C/W
R _{θJA}	Thermal Resistance, Junction to Ambient, Max.	40	

PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Marking	Package	Packing Method	Reel Size	Tape Width	Quantity
NTH4L067N65S3H	T067N65S3H	TO-247 A04	Tube	N/A	N/A	30 Units

NTH4L067N65S3H

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
OFF CHARACTERISTICS						
BV _{DSS}	Drain to Source Breakdown Voltage	$V_{GS} = 0 \text{ V}$, $I_D = 1 \text{ mA}$, $T_J = 25^\circ\text{C}$	650	–	–	V
		$V_{GS} = 0 \text{ V}$, $I_D = 1 \text{ mA}$, $T_J = 150^\circ\text{C}$	700	–	–	V
$\Delta V_{DSS} / \Delta T_J$	Breakdown Voltage Temperature Coefficient	$I_D = 10 \text{ mA}$, Referenced to 25°C	–	0.63	–	$^\circ\text{C}$
		$V_{DS} = 650 \text{ V}$, $V_{GS} = 0 \text{ V}$	–	–	2	μA
I _{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 520 \text{ V}$, $T_C = 125^\circ\text{C}$	–	1.6	–	
		$V_{GS} = \pm 30 \text{ V}$, $V_{DS} = 0 \text{ V}$	–	–	± 100	nA
I _{GSS}	Gate to Body Leakage Current					
ON CHARACTERISTICS						
$V_{GS(\text{th})}$	Gate Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 3.9 \text{ mA}$	2.4	–	4.0	V
R _{D(on)}	Static Drain to Source On Resistance	$V_{GS} = 10 \text{ V}$, $I_D = 20 \text{ A}$	–	55	67	$\text{m}\Omega$
g _{FS}	Forward Transconductance	$V_{DS} = 20 \text{ V}$, $I_D = 20 \text{ A}$	–	28	–	S
DYNAMIC CHARACTERISTICS						
C _{iss}	Input Capacitance	$V_{DS} = 400 \text{ V}$, $V_{GS} = 0 \text{ V}$, $f = 250 \text{ kHz}$	–	3750	–	pF
C _{oss}	Output Capacitance		–	60	–	pF
C _{oss(eff.)}	Effective Output Capacitance	$V_{DS} = 0 \text{ V}$ to 400 V , $V_{GS} = 0 \text{ V}$	–	691	–	pF
C _{oss(er.)}	Energy Related Output Capacitance	$V_{DS} = 0 \text{ V}$ to 400 V , $V_{GS} = 0 \text{ V}$	–	107	–	pF
Q _{g(tot)}	Total Gate Charge at 10 V	$V_{DS} = 400 \text{ V}$, $I_D = 20 \text{ A}$, $V_{GS} = 10 \text{ V}$ (Note 4)	–	80	–	nC
Q _{gs}	Gate to Source Gate Charge		–	21	–	nC
Q _{gd}	Gate to Drain "Miller" Charge		–	20	–	nC
ESR	Equivalent Series Resistance	$f = 1 \text{ MHz}$	–	0.6	–	Ω
SWITCHING CHARACTERISTICS						
t _{d(on)}	Turn-On Delay Time	$V_{DD} = 400 \text{ V}$, $I_D = 20 \text{ A}$, $V_{GS} = 10 \text{ V}$, $R_g = 4.7 \Omega$ (Note 4)	–	28	–	ns
t _r	Turn-On Rise Time		–	7.2	–	ns
t _{d(off)}	Turn-Off Delay Time		–	81	–	ns
t _f	Turn-Off Fall Time		–	2.6	–	ns
SOURCE-DRAIN DIODE CHARACTERISTICS						
I _S	Maximum Continuous Source to Drain Diode Forward Current	–	–	40	–	A
I _{SM}	Maximum Pulsed Source to Drain Diode Forward Current	–	–	112	–	A
V _{SD}	Source to Drain Diode Forward Voltage	$V_{GS} = 0 \text{ V}$, $I_{SD} = 20 \text{ A}$	–	–	1.2	V
t _{rr}	Reverse Recovery Time	$V_{GS} = 0 \text{ V}$, $I_{SD} = 20 \text{ A}$, $dI_F/dt = 100 \text{ A}/\mu\text{s}$	–	411	–	ns
Q _{rr}	Reverse Recovery Charge		–	7.8	–	μC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

TYPICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs. Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 5. Capacitance Characteristics









Figure 6. Gate Charge Characteristics

TYPICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)



NTH4L067N65S3H

TYPICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)




Figure 12. Transient Thermal Impedance




Figure 13. Gate Charge Test Circuit & Waveform




Figure 14. Resistive Switching Test Circuit & Waveforms




Figure 15. Unclamped Inductive Switching Test Circuit & Waveforms

NTH4L067N65S3H





Figure 16. Peak Diode Recovery dv/dt Test Circuit & Waveforms

SUPERFET and FRFET are a registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

PACKAGE DIMENSIONS

TO-247-4LD
CASE 340CJ
ISSUE A



NOTES:

- A. NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
- B. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- C. ALL DIMENSIONS ARE IN MILLIMETERS.
- D. DRAWING CONFORMS TO ASME Y14.5-2009.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.80	5.00	5.20
A1	2.10	2.40	2.70
A2	1.80	2.00	2.20
b	1.07	1.20	1.33
b1	1.20	1.40	1.60
b2	2.02	2.22	2.42
c	0.50	0.60	0.70
D	22.34	22.54	22.74
D1	16.00	16.25	16.50
D2	0.97	1.17	1.37
e	2.54 BSC		
e1	5.08 BSC		
E	15.40	15.60	15.80
E1	12.80	13.00	13.20
E/2	4.80	5.00	5.20
L	18.22	18.42	18.62
L1	2.42	2.62	2.82
p	3.40	3.60	3.80
p1	6.60	6.80	7.00
Q	5.97	6.17	6.37
S	5.97	6.17	6.37

onsemi, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support:

Voice Mail: 1 800-282-9855 Toll Free USA/Canada
Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

