

Terminal Part Number: 13804118
Surface Plating: SN
Material Thickness [mm]: 0,32
Cross Section [mm²]: 0,13

*This document is non-contractual
and for information only.*



*For more information, please
consult your local sales office*

Cable Type codes: 2046
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 0,81 - 0,95
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2046 0,13		0,88	50	0,86	0,03	1,45	0,03	1,30	0,10	1,60	0,10

Cable type code legend:

2046: CHFUS, FLMU142Y
Industry Designator: ISO
Conductor Material: ALLOY - DP
Conductor Plating: NONE
Insul. Material: PPE, PVC
Insul. Wall Designator: ULTRA THIN



Terminal Part Number: 13804118
Surface Plating: SN
Material Thickness [mm]: 0,32
Cross Section [mm²]: 0,13

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2085
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 0,95 - 1,00
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2085 0,13		0,98	50	0,86	0,03	1,45	0,03	1,30	0,10	1,60	0,10

Cable type code legend:

2085:

Industry Designator: DIN
Conductor Material: ALLOY - DP
Conductor Plating: NONE
Insul. Material: PVC
Insul. Wall Designator: THIN

