

NVMFS5A140PLZ

MOSFET – Power, Single P-Channel -40 V, -140 A, 4.2 mΩ



ON Semiconductor®

www.onsemi.com

Features

- Small Footprint (5 x 6 mm) for Compact Design
- Low $R_{DS(on)}$ to Minimize Conduction Losses
- NVMFS5A140PLZW: Wettable Flank Option for Enhanced Optical Inspection
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

SPECIFICATION MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise noted) (Notes 1, 2, 3)

| Symbol | Parameter | | Value | Unit | |
|-------------------|------------------------------------------------------------------------------------------------------|--------------------------------------------------|--------------------------|------|---|
| V_{DSS} | Drain to Source Voltage | | -40 | V | |
| V_{GS} | Gate to Source Voltage | | ± 20 | V | |
| I_D | Continuous Drain, Current $R_{\theta,JC}$, (Notes 1, 3) | Steady State | $T_C = 25^\circ\text{C}$ | -140 | A |
| P_D | Power Dissipation $R_{\theta,JC}$ (Note 1) | | $T_C = 25^\circ\text{C}$ | 200 | W |
| I_D | Continuous Drain: Current $R_{\theta,JA}$ (Notes 1, 2, 3) | Steady State | $T_A = 25^\circ\text{C}$ | -20 | A |
| P_D | Power Dissipation $R_{\theta,JA}$ (Note 1, 2) | | $T_A = 25^\circ\text{C}$ | 3.8 | W |
| I_{DP} | Pulsed Drain Current | $PW \leq 10 \mu\text{s}$, duty cycle $\leq 1\%$ | -560 | A | |
| T_J , T_{STG} | Operating Junction and Storage Temperature | | -55 to +175 | °C | |
| I_S | Source Current (Body Diode) | | -140 | A | |
| E_{AS} | Single Pulse Drain to Source Avalanche Energy ($L = 1.0 \text{ mH}$, $I_{L(pk)} = -29 \text{ A}$) | | 420 | mJ | |
| T_L | Lead Temperature for Soldering Purposes (1/8" from case for 10 s) | | 260 | °C | |


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS


| Symbol | Parameter | Value | Unit |
|-----------------|-------------------------------------------|-------|------|
| $R_{\theta,JC}$ | Junction to Case Steady State | 0.75 | °C/W |
| $R_{\theta,JA}$ | Junction to Ambient Steady State (Note 2) | 39 | |

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
2. Surface mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

| V_{DSS} | $R_{DS(on)} \text{ MAX}$ | $I_D \text{ MAX}$ |
|-----------|--------------------------|-------------------|
| -40 V | 4.2 mΩ @ -10 V | -140 A |
| | 7.2 mΩ @ -4.5 V | |



MARKING DIAGRAM



XXXXXX = Specific Device Code
5A140L(NVMFS5A140PLZ)
140LWF(NVMFS5A140PLZW)
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

See detailed ordering and shipping information on page 7 of this data sheet.

NVMFS5A140PLZ

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

| Symbol | Parameter | Test Condition | Min | Typ | Max | Unit |
|--------|-----------|----------------|-----|-----|-----|------|
|--------|-----------|----------------|-----|-----|-----|------|

OFF CHARACTERISTICS

| | | | | | | |
|----------------------|-----------------------------------|------------------------------------------------|------------------------------------|--|------|----|
| V _{(BR)DSS} | Drain to Source Breakdown Voltage | I _D = -1 mA, V _{GS} = 0 V | -40 | | | V |
| I _{DSS} | Zero Gate Voltage Drain Current | V _{DS} = -40 V, V _{GS} = 0 V | T _J = 25°C | | -1.0 | μA |
| | | | T _J = 100°C (Note 4) | | -100 | μA |
| I _{GSS} | Gate to Source Leakage Current | V _{GS} = ±16 V, V _{DS} = 0 V | | | ±10 | μA |

ON CHARACTERISTICS (Note 5)

| | | | | | | |
|---------------------|-------------------------------|-------------------------------------------------|------------------------|--|------|-----|
| V _{GS(th)} | Gate Threshold Voltage | V _{DS} = -10 V, I _D = -1 mA | -1.2 | | -2.6 | V |
| R _{DS(on)} | Drain to Source On Resistance | V _{GS} = -10 V | I _D = -50 A | | 3.2 | 4.2 |
| | | V _{GS} = -4.5 V | I _D = -50 A | | 5.0 | 7.2 |
| g _{FS} | Forward Transconductance | V _{DS} = -10 V, I _D = -50 A | | | 125 | S |

CHARGES, CAPACITANCES & GATE RESISTANCE

| | | | | | | | |
|---------------------|------------------------------|-------------------------------------------------|--|--|------|--|----|
| C _{iss} | Input Capacitance | V _{GS} = 0 V, f = 1 MHz | | | 7400 | | pF |
| C _{oss} | Output Capacitance | V _{DS} = -20 V, | | | 1030 | | |
| C _{rss} | Reverse Transfer Capacitance | | | | 720 | | |
| Q _{g(tot)} | Total Gate Charge | V _{GS} = -10 V, I _D = -50 A | | | 136 | | nC |
| Q _{gs} | Gate to Source Charge | V _{DS} = -20 V, | | | 26 | | |
| Q _{gd} | Gate to Drain Charge | | | | 31 | | |

SWITCHING CHARACTERISTICS (Note 6)

| | | | | | | | |
|---------------------|---------------------|--------------------------------------------------|--|--|-----|--|----|
| t _{d(on)} | Turn-On Delay Time | V _{DS} = -20 V, I _D = -50 A, | | | 50 | | ns |
| t _r | Rise Time | V _{GS} = -10 V, R _G = 50 Ω | | | 860 | | |
| t _{d(off)} | Turn-Off Delay Time | | | | 540 | | |
| t _f | Fall Time | | | | 740 | | |

DRAIN-SOURCE DIODE CHARACTERISTICS

| | | | | | | | |
|-----------------|-------------------------|-------------------------------------------------------------------|--|--|-------|------|----|
| V _{SD} | Forward Diode Voltage | V _{GS} = 0 V, I _S = -50 A | | | -0.83 | -1.5 | V |
| t _{rr} | Reverse Recovery Time | V _{GS} = 0 V, I _S = -50 A di/dt = 100 A/μs | | | 108 | | ns |
| Q _{rr} | Reverse Recovery Charge | | | | 236 | | nC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. The maximum value is specified by design at T_J = 100 °C. Product is not tested to this condition in production.
5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2 %.
6. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 1. I_D – V_{DS}




Figure 2. I_D – V_{GS}




Figure 3. $R_{DS(on)}$ – V_{GS}




Figure 4. $R_{DS(on)}$ – T_J




Figure 5. I_S – V_{SD}




Figure 6. SW Time – I_D

TYPICAL CHARACTERISTICS




Figure 7. C_{iss} , C_{oss} , C_{rss} – V_{DS}




Figure 8. V_{GS} – Q_g




Figure 9. SOA




Figure 10. I_{PEAK} – T_{AV}




Figure 11. P_D – T_c

NVMFS5A140PLZ

TYPICAL CHARACTERISTICS





Figure 12. $R_{\theta JA}$ - Pulse Time

NVMFS5A140PLZ

ORDERING INFORMATION

| Device | Marking | Package | Shipping (Qty / Packing) [†] |
|--------------------|---------|---------------------------------------------------------|---------------------------------------|
| NVMFS5A140PLZT1G | 5A140L | DFN5 5x6, 1.27P (SO-8FL) (Pb-Free) | 1.500 / Tape & Reel |
| NVMFS5A140PLZWFT1G | 140LWF | DFN5 5x6, 1.27P (SO-8FL) (Pb-Free / Wettable Flanks) | 1.500 / Tape & Reel |
| NVMFS5A140PLZT3G | 5A140L | DFN5 5x6, 1.27P (SO-8FL) (Pb-Free) | 5.000 / Tape & Reel |
| NVMFS5A140PLZWFT3G | 140LWF | DFN5 5x6, 1.27P (SO-8FL) (Pb-Free / Wettable Flanks) | 5.000 / Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.



SCALE 2:1


DFN5 5x6, 1.27P
(SO-8FL)
CASE 488AA
ISSUE N

DATE 25 JUN 2018

NOTES:


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH PROTRUSIONS OR GATE BURRS.

| DIM | MILLIMETERS | | |
|-----|-------------|-------|------|
| | MIN | NOM | MAX |
| A | 0.90 | 1.00 | 1.10 |
| A1 | 0.00 | ---- | 0.05 |
| b | 0.33 | 0.41 | 0.51 |
| c | 0.23 | 0.28 | 0.33 |
| D | 5.00 | 5.15 | 5.30 |
| D1 | 4.70 | 4.90 | 5.10 |
| D2 | 3.80 | 4.00 | 4.20 |
| E | 6.00 | 6.15 | 6.30 |
| E1 | 5.70 | 5.90 | 6.10 |
| E2 | 3.45 | 3.65 | 3.85 |
| e | 1.27 BSC | | |
| G | 0.51 | 0.575 | 0.71 |
| K | 1.20 | 1.35 | 1.50 |
| L | 0.51 | 0.575 | 0.71 |
| L1 | 0.125 REF | | |
| M | 3.00 | 3.40 | 3.80 |
| θ | 0 ° | ---- | 12 ° |




DETAIL A

SEATING PLANE



DETAIL A



STYLE 1:
PIN 1. SOURCE
2. SOURCE
3. SOURCE
4. GATE
5. DRAIN

STYLE 2:
PIN 1. ANODE
2. ANODE
3. ANODE
4. NO CONNECT
5. CATHODE

DIMENSIONS: MILLIMETERS

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

| | | |
|------------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON14036D | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION: | DFN5 5x6, 1.27P (SO-8FL) | PAGE 1 OF 1 |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

