





PRODUCT NUMBER	PITCH
VMxx55x100J0G	5.08 mm



Material:

- Item① Clamp: Steel zinc plated.
- Item② Terminal screw: Steel Zinc plating "-" slot type
- Item③ Female contact: High conductivity copper Tin plated
- Item④ Terminal (top body): Thermoplastic (UL94V-0)
- Item⑤ Terminal (bottom body): Thermoplastic (UL94V-0)
- Item⑥ Steel block: Steel Zinc plated

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range: 0.34-2.5mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus

DIMENSION

Dim A	N×5.08
Dim B	(N-1)×5.08

N=Number of poles

Poles	Tolerance
2p-6p	±0.20
7p-12p	±0.25
13p-18p	±0.30
19p-24p	±0.40

PART NO.: VM xx 55 x 1 00J0 G

		Color	RoHS compliant (lead<4%) In copper Alloy
Solid block	0	Black (RAL9005)	
No. of poles	2	Red (RAL3001/D)	
02 2 poles	3	Orange(RAL2011/P)	
03 3 poles	4	Yellow(RAL1018/A)	
...	5	Green(RAL6018/T)	
24 24 poles	6	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn no	dr	date				TERMINAL BLOCK			
B	T-19283	HF	081414				TERMINAL BLOCK			
				angles	X.±0.5	MM	PLUGGABLE PLUG, WITHOUT FLANGE, LOW PROFILE			
					X.X±0.3					
				X'±1"	X.XX±0.1	scale				
		dr	EVIN ZHONG	042114		FCI	dwg no			
		enr	EVIN ZHONG	042114			sheet 1 of 1 size			
		chr	HANKE FENG	042114			VMxx55x100J0G			
		appd	SHI JUN	042114			A4			
sheet index	revision	B					type			
	sheet	1					CUSTOMER Drawing			