



**Part Number :** [1200700171](#)

**Product Description :** M12 Signal, A-Coded, Receptacle, 4 Poles, Female, Front Panel Mount, 1/2"-14 NPT Mounting Threads, 18 AWG, PVC Leads, 3.0m (9.84') Length

**Series Number :** 120070

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** 8R4000A16M030



---

## Documents and Resources


### Drawings

[1200700171\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Triphenyl-phosphate per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	120070
Description	M12 Signal, A-Coded, Receptacle, 4 Poles, Female, Front Panel Mount, 1/2"-14 NPT Mounting Threads, 18 AWG, PVC Leads, 3.0m (9.84') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	M12 Signal, Micro-Change (M12)
Type	Single Ended (pigtail)
UPC	78678883492

### Agency

CSA	LR6837
UL	E152210

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

### Physical

Coupling Type	Internal Thread
Gender	Female

Keyway	A-Coded
Length	3.0m
Material - Component	Nickel-plated Zinc Die-Cast
Mounting Thread Size	1/2" - 14 NPT
Net Weight	174.200/g
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	PVC Leads, UL 1569
Wire Size (AWG)	18

---

This document was generated on Apr 23, 2026