


Cement Resistors



INTRODUCTION

The materials used and the construction techniques ensure excellent flame resistance, arc resistance and moisture resistance as well as self-extinguishing capabilities. They will withstand the most rigorous loading test.

As resistors in radio and television receivers, hazardous conditions such as smoking and redheat can be completely prevented by the proper choice of power resistors.


Low Ohmic Metal Plate Type

Normal Style [SLR Series]


FEATURES

Power Rating	2W, 3W, 5W, 7W, 10W, 3W+3W, 5W+5W
Resistance Tolerance	$\pm 5\%$, $\pm 10\%$
T.C.R.	$\pm 250\text{ppm}/^\circ\text{C}$

DERATING CURVE




TEMPERATURE RISE



DIMENSIONS

Unit: mm



STYLE	DIMENSION					
Normal	A	B	C	D	ϕd	RM
SLR200	8 ± 1	13 ± 1	3.5 ± 1	5 ± 1	0.06 ± 0.05	9 ± 1
SLR300	13 ± 1	13 ± 1	3.5 ± 1	5 ± 1	0.06 ± 0.05	9 ± 1
SLR500	18 ± 1	14 ± 1	3.5 ± 1	5 ± 1	0.06 ± 0.05	10 ± 1
SLR700	18 ± 1	26 ± 1	3.5 ± 1	5 ± 1	0.08 ± 0.05	20 ± 1
SLR10A	20 ± 1	26 ± 1	3.5 ± 1	5 ± 1	0.08 ± 0.05	20 ± 1
SLR303	18 ± 1	26 ± 1	12 ± 1	5 ± 1	0.08 ± 0.05	10 ± 1
SLR505	20 ± 1	26 ± 1	12 ± 1	5 ± 1	0.08 ± 0.05	10 ± 1

Note:

ELECTRICAL CHARACTERISTICS

STYLE	SLR200	SLR300	SLR500	SLR700	SLR10A	SLR303	SLR505
Power Rating at 40°C		3W	5W	7W	10W	3W+3W	5W+5W
Power Rating at 70°C	2W						
Maximum Working Voltage		$\sqrt{P_x R}$					
Dielectric Withstanding Voltage	500V	700V		1,000V		700V	
Resistance range	0.10Ω - 0.68Ω	0.01Ω - 1Ω	0.01Ω - 3.3Ω			(0.1Ω+0.1Ω) - (0.5Ω+0.5Ω)	(0.1Ω+0.1Ω) - (1.8Ω+1.8Ω)
Operating Temp. Range	-55°C to +155°C						
Temperature Coefficient	±250ppm/°C						

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD	APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 Sec.
Voltage Proof on Insulation	IEC 60115-1 4.7	in V-block for 60 Sec., test voltage by type
Temperature Coefficient	IEC 60115-1 4.8	-55°C to +155°C
Insulation Resistance	IEC 60115-1 4.6	in V-block for 60 Sec.
Solderability	IEC 60115-1 4.17	235±5°C for 3±0.5 Sec.
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV for 1,000 Hr. (1.5 Hr. on, 0.5 Hr. off)
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇒ Room Temp. ⇒ +155°C ⇒ Room Temp. (5 cycles)
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body

Note: RCWV(Rated Continuous Working Voltage) = $\sqrt{Power\ Rating \times Resistance\ Value}$ or Max. working voltage listed above, whichever less.

Revision: 201304



EXPLANATIONS OF ORDERING CODE

MFR	-12	F	T	F	52-	100R
<p>Code 1 - 3 Series Name See Index</p> <p>-05 = ød0.5mm -06 = ød0.6mm -07 = ød0.7mm -08 = ød0.8mm -10 = ød1.0mm -14 = ød1.4mm -12 = 1/6W -25 = 1/4W 25S = 1/4WS -50 = 1/2W 50S = 1/2WS 100 = 1W 1WS = 1WS 200 = 2W 2WS = 2WS 204 = 0.4W 207 = 0.6W 300 = 3W 3WS = 3WS 3WM = 3WM 400 = 4W 500 = 5W 5WS = 5WS 5SS = 5WSS 700 = 7W 7WS = 7WS 10A = 10W 20A = 20W 30A = 30W 40A = 40W 50A = 50W 10S = 10WS 15A = 15W 25A = 25W 10B = 100W 25B = 250W</p>	<p>Code 4 - 6 Power Rating</p> <p>-05 = ød0.5mm -06 = ød0.6mm -07 = ød0.7mm -08 = ød0.8mm -10 = ød1.0mm -14 = ød1.4mm -12 = 1/6W -25 = 1/4W 25S = 1/4WS -50 = 1/2W 50S = 1/2WS 100 = 1W 1WS = 1WS 200 = 2W 2WS = 2WS 204 = 0.4W 207 = 0.6W 300 = 3W 3WS = 3WS 3WM = 3WM 400 = 4W 500 = 5W 5WS = 5WS 5SS = 5WSS 700 = 7W 7WS = 7WS 10A = 10W 20A = 20W 30A = 30W 40A = 40W 50A = 50W 10S = 10WS 15A = 15W 25A = 25W 10B = 100W 25B = 250W</p>	<p>Code 7 Tolerance</p> <p>P = ±0.02 % A = ±0.05 % B = ±0.1 % C = ±0.25 % D = ±0.5 % F = ±1 % G = ±2 % J = ±5 % K = ±10 % - = Base on Spec.</p>	<p>Code 8 Packing Style</p> <p>T = Tape/Box R = Tape/Reel B = Bulk</p>	<p>Code 9 Temperature Coefficient of Resistance</p> <p>- = Base on Spec. A = ±5 ppm/°C B = ±10 ppm/°C C = ±15 ppm/°C S = ±20 ppm/°C D = ±25 ppm/°C E = ±50 ppm/°C F = ±100 ppm/°C G = ±200 ppm/°C H = ±250 ppm/°C I = ±300 ppm/°C J = ±350 ppm/°C</p>	<p>Code 10 - 12 Forming Type</p> <p>26- = 26mm 52- = 52.4mm 73- = 73mm 81- = 81mm 91- = 91mm F = F Type FK = FK Type FKK = FKK Type FFK = F-form Kink M = M-Type Forming MB = M-form W/flat MT = MT Type Forming MR = MR Type AV = AV Insert PN = PANASert</p>	<p>Code 13 - 17 Resistance Value</p> <p>0R1 = 0.1 100R = 100 10K = 10,000 10M = 10,000,000</p>

EXCEPTION:

• Cement series:

<Code 8>: Special packing style code

B: Bulk with wirewound or metal oxide sub-assembly for resistance value

W: Bulk with ceramic based wirewound sub-assembly for resistance value

M: Bulk with metal oxide sub-assembly for resistance value

F: Bulk with Fiberglass based wirewound sub-assembly for resistance value

<Code 10-12>: Without forming code

Example: SQP500**J**-10R

• JPW series:

<Code 13-17>: without resistance value code

Example: **JPW-06-T-52-**