








PRELIMINARY

spec ref				dr		LI-Qing Lei	2015/04/02	projection		MM		size		A3	scale		6.000					
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng						LI-Qing Lei	2015/04/02	ecn no				-				
						chr						-	-	rel level				Preliminary				
						appr						-	-					product family				
surface		linear		0.X	±0.25			title		USB3.1 Type-C				dwg no		10133477				rev		1
				0.XX	±0.15																	
				0.XXX	±0.10																	
		angular		0°	±2°	www.fci.com		cat. no.				Product - Customer Drw				sheet 1 of 2						



NOTE :

1. MATERIAL:

- 1.1 HOUSING: THERMOPLASTIC, BLACK, UL94V-0
1.2 TERMINAL: COPPER ALLOY
1.3 SHELL: STAINLESS STEEL
1.4 TOP EMI PLATE: STAINLESS STEEL
1.5 BOTTOM EMI PLATE: STAINLESS STEEL
1.6 MID PLATE: STAINLESS STEEL

2. PLATING:

- 2.1 TERMIAL: (Min) 0.05 μ m Au + (Min) 0.75 μ m Ni-Pd ON
CONTACT AREA
- 2.2 SHELL/EMI PLATE/MID-PLATE/: PLATING 0.74 μ m MIN NI
OVER AREA.

3. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW ;

4. LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008

5. PRODUCT MEET HALOGEN FREE

- 6 PART NUMBER CODE: 10133477-1000ILF

PIN ASSIGNMENTS			
PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	A1	GND
A2	SSTX _{p1}	A2	SSRX _{p1}
A3	SSTX _{n1}	A3	SSRX _{n1}
A4	VBUS	A4	VBUS
A5	CC1	A5	SBU2
A6	D _{p1}	A6	D _{n2}
A7	D _{n1}	A7	D _{p2}
A8	SBU1	A8	CC2
A9	VBUS	A9	VBUS
A10	SSRX _{n2}	A10	SSTX _{n2}
A11	SSRX _{p2}	A11	SSTX _{p2}
A12	GND	A12	GND

PRELIMINARY

spec ref				dr		Li-Qing Lei		2015/04/02		projection				MM		size		A3		scale		4.000															
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED						eng		Li-Qing Lei		2015/04/02																									
								chr		-		-																									
								appr		-		-		product family						ecn no						-											
surface 		linear		0.X		±0.25				title						USB3.1 Type-C						dwg no						10133477						rev		1	
				0.XX		±0.15																															
				0.XXX		±0.10																															
		angular		0°		±2°		www.fci.com		cat. no.						Product - Customer Drw						sheet 2 of 2															