



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 30MAR11 CHK SAM MACE 30MAR11 APVD SAM MACE 30MAR11		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MTA-100 HEADER ASSY, SURFACE MOUNT, FRICTION LOCK, TAPE LOADED W/CAP —	
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .015 4 PLC ± — ANGLES ± 1°		PRODUCT SPEC 108-1050 APPLICATION SPEC 114-1019	
MATERIAL —		FINISH —		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
				DRAWING NO C-1744163	
				RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 3:1	
				SHEET 1 of 6	
				REV C	

1744163

1

A





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


D

C





B

A





32.00 [1.260]	972366-4	1706504-4	147117-5	4	3-647168-4	3-1744163-4			
DIM "A"	COVER TAPE	CARRIER TAPE	PICK & PLACE CAP	NO. OF POSITIONS	HEADER ASSEMBLY	PART NO			
	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth	30MAR11	 TE Connectivity				
			CHK SAM MACE	30MAR11					
			APVD SAM MACE	30MAR11					
	DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				
		0 PLC	± -	PRODUCT SPEC		MTA-100 HEADER ASSY, SURFACE MOUNT, FRICTION LOCK, TAPE LOADED W/CAP -			
		1 PLC	± -	108-1050					
		2 PLC	± -	APPLICATION SPEC					
3 PLC		± .015	114-1019						
4 PLC	± -			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL		FINISH	WEIGHT		A2	00779	C-1744163	-	
			CUSTOMER DRAWING				SCALE 3:1	SHEET 2 of 6	REV C

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




24.00 [0.945]	972366-3	1706504-3	147117-5	3	3-647168-3	3-1744163-3
DIM "A"	COVER TAPE	CARRIER TAPE	PICK & PLACE CAP	NO. OF POSITIONS	HEADER ASSEMBLY	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30MAR11 jr ruth CHK 30MAR11		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: APVD SAM MACE 30MAR11 SAM MACE PRODUCT SPEC 108-1050 APPLICATION SPEC 114-1019		NAME MTA-100 HEADER ASSY, SURFACE MOUNT, FRICTION LOCK, TAPE LOADED W/CAP -	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .015 4 PLC ± - ANGLES ± 1°		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-1744163 -	
MATERIAL -		FINISH -		WEIGHT -	
CUSTOMER DRAWING				SCALE 3:1 SHEET 3 of 6 REV C	



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN jr ruth CHK SAM MACE APVD SAM MACE PRODUCT SPEC 108-1050 APPLICATION SPEC 114-1019	30MAR11 30MAR11 30MAR11	 TE Connectivity				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		MTA-100 HEADER ASSY, SURFACE MOUNT, FRICTION LOCK, TAPE LOADED W/CAP —			
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .015 4 PLC ± — ANGLES ± 1°				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL —		FINISH —		WEIGHT		A2	00779	C-1744163	—
CUSTOMER DRAWING						SCALE	3:1	SHEET	4 OF 6
						REV C			



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B

B

A

A



CAP FOR HEADER

1744163

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN jr ruth 30MAR11 CHK SAM MACE 30MAR11 APVD SAM MACE 30MAR11 PRODUCT SPEC 108-1050 APPLICATION SPEC 114-1019 WEIGHT CUSTOMER DRAWING		TE Connectivity NAME MTA-100 HEADER ASSY, SURFACE MOUNT, FRICTION LOCK, TAPE LOADED W/CAP - SIZE A2 CAGE CODE 00779 DRAWING NO C=1744163 RESTRICTED TO - SCALE 3:1 SHEET 6 of 6 REV C					
DIMENSIONS: mm [INCHES]			TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.40[.015] 3 PLC ± - 4 PLC ± - ANGLES ± 1°							
MATERIAL -									FINISH -	