

TOSHIBA Photo-Interrupter Infrared LED + Photo IC

TLP1252(C6,F)

Lead-Free Product


Copiers, Printers, Fax Machines

Air-Conditioners

Game Machines


The TLP1252(C6,F) is a compact photo-interrupter with a built-in connector that uses a high radiant power GaAs infrared LED and a Si photo-IC. The device is housed in a highly reliable package which eliminates the need for a printed circuit board or for soldering. It is ideal for use as a paper carrier location sensor for copiers and printers. As the device can operate at temperatures of up to 95°C, it can be used for high-temperature applications such as paper-out sensors. When the light is shielded, outputs are at low level.

- High reliability package (PWB-less, soldering-less)
- Small package
- Snap-in installation
- Three board thicknesses supported: (1.0mm, 1.2mm, 1.6mm)
- Gap: 5mm
- Resolution: Slit width 0.5mm
- High-temperature operation: $T_{opr} = 95^{\circ}\text{C}(\text{max.})$
- Low current consumption: $I_{CC} = 14 \text{ mA}(\text{max.})$
- Digital output (open collector)
- CT connector (2-mm pitch MT receptacle type, MT crimp receptacle type II) made by Tyco Electronics AMP, Ltd.
- Package material: Body.....Polycarbonate (UL94V-2, black)
: Connector.....66 nylon (UL94V-0, white)



Weight: 1.3 g (typ.)

Product Indication



Maximum Ratings (Ta = 25°C)

Characteristic	Symbol	Rating	Unit
Supply voltage	V_{CC}	7.5	V
Output voltage	V_O	15	V
Low level output current	I_{OL}	16	mA
Low level output current derating (Ta > 76°C)	$\Delta I_{OL} / ^\circ\text{C}$	-0.67	mA / °C
Operating temperature range	T_{opr}	-30~95	°C
Storage temperature range	T_{stg}	-40~100	°C

Recommended Operating Conditions


Characteristic	Symbol	Min	Typ.	Max	Unit
Supply voltage	V_{CC}	4.5	5.0	5.5	V
Output voltage	V_O	—	5.0	13.2	V
Low level output current	I_{OL}	—	—	16	mA

Opto-Electrical Characteristics

(unless otherwise specified, Ta = -30~95°C, $V_{CC} = 5V \pm 10\%$)


Characteristic	Symbol	Test Condition	Min	Typ.	Max	Unit
Supply voltage	V_{CC}		4.5	5	5.5	V
Supply current	High level	I_{CCH} When light is detected	—	—	14	mA
	Low level	I_{CCL} When light is shielded	—	—	14	
Output voltage	High level	V_{OH} When light is detected, $R_L = 47k\Omega$	$0.9V_{CC}$	—	—	V
	Low level	V_{OL} When light is shielded, $I_{OL} = 16\text{mA}$, Ta = 25°C	—	0.07	0.35	V
		When light is shielded, $I_{OL} = 16\text{mA}$	—	—	0.4	
Peak emission wavelength	λ_P	Ta = 25°C, LED side	—	940	—	nm
Peak sensitivity wavelength	λ_P	Ta = 25°C, Photo IC side	—	900	—	nm
Response frequency	f	$R_L = 4.7k\Omega$, Ta = 25°C, (Note)	5	—	—	kHz
Rise time	t_r		—	0.8	—	
Fall time	t_f		—	0.04	—	

(Note): The response frequency is measured while the shutter is rotated as shown below. There should be no DC output.



Terminal Strength (Ta = 25°C)

Characteristic		Test Condition		Limit
Terminal strength	Pull	Direction	A	No defect of electrical characteristics
		Weight	19.6N	
		Time	5s / once	
	Bend	Direction	B	
		Weight	9.8N	
		Time	5s / three times	



Matched Connector

Tyco Electronics AMP Ltd. made CT connector(2mm pitch MT receptacle type)

Housing–Terminal En Block Type	Type no.	Terminal Material	AWG Size	External Diameter of Insulation Coating
	173977–3	Phosphor bronze	AWG26~28	0.85~1.05mm

Tyco Electronics AMP Ltd. made CT connector(2mm pitch MT crimp receptacle type II)

Housing	179228–3				
Terminal	Type no.	Product Form	Material	AWG Size	External Diameter of Insulation Coating
	179518–1	Bulk	Phosphor bronze	AWG22~26	0.93~1.5mm
	179227–1	Coupled			

For more details of connector characteristics, please contact the relevant connector manufacturer.

Precautions

1. When VCC is turned on, it takes at least 100 μ s for the internal circuit to stabilize.
During this time the output signal is unstable. Please do not use the unstable signal as the output signal.
2. Protect the device from ambient light interference. The integrated photo-IC is insensitive to light below 700 nm (e.g. fluorescent light), but is sensitive to light above 700 nm (e.g. incandescent light). If it detects ambient light, it may cause malfunction. Be sure to make a thorough evaluation of the equipment in which the device is to be used.
3. The environment to install the device should be determined carefully. Oil or chemicals may cause the package to be dissolved or cracked.
4. When installing, avoid to work by holding the connector by hand. Always, install by holding the main body of the device while assuring the metal board is not warped or twisted. The connectors should be inserted or removed at room temperature.
5. Toshiba recommends attaching the device to the smoother side of the board.
6. Toshiba recommends testing the attachment strength beforehand by actually attaching a device to the board.
7. Do not apply solder to the pins of the device's connector. Make sure that the connector is plugged into the CT connector.
8. When inserting or removing the CT connector, always grasp it and its cable firmly and either plug it straight into or pull it straight out of the device's connector. If the CT connector is inserted or removed at an angle, both the device's connector and the CT connector may get damaged, resulting in an unreliable connection.


Package Dimensions: TOSHIBA 11–15E2

Unit in mm

() : REFERENCE VALUE


UNLESS OTHERWISE SPECIFIED





DIMENSION	TOLERANCE
6 >	±0.1
6 < 14	±0.2



Weight : 1.3 g (typ.)


Pin Connection





Relative Positioning of Shutter and Device

For normal operation, position the shutter and the device as shown in the figure below. By considering the device's detection direction characteristic and switching time, determine the shutter slit width and pitch.




Unit: mm

Thickness of Metal Board	a Dimension	b Dimension
1.0	11.9min	9.4max
1.2	11.7min	9.2max
1.6	11.3min	8.8max

Recommended Size of Connection Holes

(Unit: mm)



For instructions on how to attach the device to a metal board of a type other than the ones shown above, please contact your local Toshiba sales office.

RESTRICTIONS ON PRODUCT USE

030619EAC

- The information contained herein is subject to change without notice.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations.
- GaAs(Gallium Arsenide) is used in this product. The dust or vapor is harmful to the human body. Do not break, cut, crush or dissolve chemically.