







SCALE 6 : 1



2102060-2	17	1.27µm	13	LEAD FREE PER SAC405	I-2102061-8
2102060-1	17	1.27µm	13	TIN LEAD	I-2102061-7
2102060-4	15	0.76µm	11	LEAD FREE PER SAC405	I-2102061-6
2102060-3	15	0.76µm	11	TIN LEAD	I-2102061-5
2102060-2	15	1.27µm	11	LEAD FREE PER SAC405	I-2102061-4
2102060-1	15	1.27µm	11	TIN LEAD	I-2102061-3
2102060-4	18	0.76µm	14	LEAD FREE PER SAC405	I-2102061-2
2102060-3	18	0.76µm	14	TIN LEAD	I-2102061-1
2102060-2	18	1.27µm	14	LEAD FREE PER SAC405	I-2102061-0
2102060-1	18	1.27µm	14	TIN LEAD	2102061-9
2102060-4	12	0.76µm	8	LEAD FREE PER SAC405	2102061-8
2102060-3	12	0.76µm	8	TIN LEAD	2102061-7
2102060-4	10	0.76µm	6	LEAD FREE PER SAC405	2102061-6
2102060-3	10	0.76µm	6	TIN LEAD	2102061-5
2102060-2	12	1.27µm	8	LEAD FREE PER SAC405	2102061-4
2102060-1	12	1.27µm	8	TIN LEAD	2102061-3
2102060-2	10	1.27µm	6	LEAD FREE PER SAC405	2102061-2
2102060-1	10	1.27µm	6	TIN LEAD	2102061-1
MATING PART NUMBER	MATED STACK HEIGHT (mm)	GOLD PLATING THICKNESS	H MAX REF	SOLDER BALL MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN 23JUL2009			
						S BOUTY			
						CHK K DOWNHOWER			
						APVD K DOWNHOWER			
DIMENSIONS:						TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm								ASSEMBLY, SOCKET, 114 POSITION, MEZALOK STACKING CONNECTOR	
						PRODUCT SPEC 108-2411			
						APPLICATION SPEC 114-13279			
MATERIAL						WEIGHT		SIZE CAGE CODE DRAWING NO	
FINISH								A100779C-2102061	
 1						 2		RESTRICTED TO	
CUSTOMER DRAWING						SCALE 8:1		SHEET 1 OF 1 REV M	

PCB LAYOUT (CONNECTOR SIDE)
SCALE 8:1