



REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE









NOTES1:

UL Standard

1.Rated Voltage/Current : 300V / 6.3A
2.Torque Value : M3 , 4.43Lb.in
3.Wire Range : 22~14AWG

IEC Standard

1.Rated Voltage/Current : 250V / 6.3A
2.Torque Value : M3 , 0.5N·m
3.Wire Range : 0.5~2.5mm^2

NOTES2:

1.Dimension shall be interpreted per ASME Y14.5-2009
2.Pitch : 10.00mm, Poles : N=01~05P
3.Stripping length : 6~7mm
4.Withstanding Voltage : AC2000V/1Min.
5.Operating temperature: -40°C~+105°C
6.Undimensioned Tolerances:

Pitch Range In mm			Nominal Dimension Range In mm					— ⌒ ⌓
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10 ∠
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°

7.RoHS Compliance

DG801 - XXP - 1Y - 00A (H)
- (H) — (RoHS)
- 00A — (Standard)
- (Series No.)
- (Poles)
- (Single Pitch)
- (Color): 1.(Grey) 2.(Blue) 3.(Black) 4.(Green) 5.(Orange) 6.(Red) 7.(Transparent) 8.(Yellow) 9.(White)

DETACHED LISTS	PART NO.: /	DEGSON® 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD	
	APPD: /	NAME: DG801-XXP-1Y-00A(H)	
	CHKD: /		
	DRFT: /	TITLE: CUSTOMER DRAWING	REV D0
	THIRD ANGLE PROJECTION	DRAWING NO.: /	SHEET 1/1
		MM (INCH) DO NOT SCALE DRAWING	SCALE 1:1

Downloaded from Arrow.com.