



Customize your VGA functionality by securing an efficient, fixed port. Provide access to a PC, monitor, or projector with minimal exposure or repositioning. From connections at podiums and kiosks to wall plate mounting, our panel-mount cable is a great way to keep your connections clean and professional. Featuring screw-style connectors with a molded hood, this cable provides an easy connection to a faceplate or machined port.

Constructed from premium grade shielded video cable which uses a combination of coax and twisted pair, this SXGA cable accommodates cable runs up to 100 feet without a booster (in most cases). Ideal for video presentation devices, video splitters, and KVM switches.

SXGA provides a screen resolution of 1280 x 1024 pixels. Not sure what resolution you need? See our [L path="/category/vga#compare" target="_new"]VGA resolution guide.[/L]

[B]Please Note:[/B] Pin 9 is not loaded. Pin 9 is not required for standard computer video applications.

Features & Benefits

Panel-mount connector design

Supports up to a 1280x1024 resolution

Shielded to protect from interference

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120520931	Country Of Origin	China
Application Sector	Commercial, Residential	Warranty Type	Lifetime
Type	Cable		

Dimensions

Product Length US	1.0 FT	Cable Length	1 ft
-------------------	--------	--------------	------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	SXGA (1280x1024)
-----------------	--------------------------	------------------	------------------

Shielded/Unshielded Cable	Shielded	Cable Type	Extension, Video
Jacket Rating	Standard / Non-Rated	Connector 2	VGA Female
Connector 1	VGA Male	Video Output Support	VGA
Video Input Support	VGA		