




Technical Data

Asset identification label, thermal transfer
Helatag 1206

05.09.2022

TAG69TD2-1206-WH

Article Number 596-12669



Material: Type 1206, Polyester (1206)
Colour: White gloss (GSWH)

Operating Temperature - °C: -40 °C to +150 °C
Curing Temperature: from 0 °C

Self adhesive (Yes/No): Yes

Width (W): 40.64 mm
Height (H): 22.86 mm
Width of Liner (WL): 89.00 mm
Labels per Row: 2 pcs.

Thickness of Foil: 50 µm

Test Method
ISO 534

Adhesive: Acrylic
Initial tack: 13 N
Shear strength: 1000 min

FINAT FTM 9
FINAT FTM 8

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



Technical Data

05.09.2022

Asset identification label, thermal transfer
Helatag 1206

Print Method:	Thermal transfer print
Print Method (Alternative):	Laser beam print
Application Tool:	TT431, TT4030
Recommended Ribbon Type:	TT822OUT
Shelf Life:	Minimum 1 year upon receipt / maximal 4 years after production date.
Storage Temperature:	+15 °C to +25 °C
Storage conditions:	45% ±5% relative humidity., The storage in the original packaging is recommended., Please avoid warehousing under impacts such as high humidity, heat and coldness., Must be stored in a dark place.
Application Method:	The functionality and durability of the labels can be negatively affected if improperly processed or applied. All surfaces to be bonded must be clean, dry as well as free from dust and grease. Avoid touching the adhesive surface of the label as this could impair the application performance.



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved