

6

5

4

3



2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/13/09	

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



RECOMMENDED PCB LAYOUT  
(Copper-sided view)

## SPECIFICATIONS:

## Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Bushing: Brass, Nickel plated

Contacts: Copper Alloy

## Plating:

Tin over Copper underplate

## Electrical:

Operating voltage: 30 VDC max.

Current rating: 0.5 Amp max.

Contact resistance: 30 mohms max. initial

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

## Temperature Rating:

Operating temperature: -65°C to +125°C

## Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 235°C for 5 sec.

CONTACT FORM	ASJ-7H-5-M	ASJ-7H-4B-M	ASJ-7H-3A-M	ASJ-7H-3-M
SCHEMATIC				

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
STEREO JACK  
M6 x 0.5 THREADED BUSHING

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		Holes		DATE	
.X	± .10	ØXX	± .10		
.XX	± .020	ØXXX	± .015		
.XXX	± .015	ØXXXX	± .010		
APPROVALS		DATE			
DRAWN	DY	7/13/09			
CHECKED					
APPROVED					
SIZE		PART NO.		REV.	
X		ASJ-7H-X-M		-	
REF: S00002C		SCALE: NTS		SHEET 1 OF 1	



A

B

C

D

A

B

C

D