




Product: [1540A](#) 

RISC 6000, #28-7c, BC, PO, O/A Foil+Braid, PVC Jkt, CL2

Product Description

RISC 6000 IBM XX, YY Cable, 28 AWG stranded (7x36) bare copper conductors, patented step polyolefin insulation, twisted pairs, overall Beldfoil® shielded + tinned copper braid shield (65% coverage), tinned copper drain wire, PVC jacket (see RISC color code chart below).

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
28	7x36	BC - Bare Copper	7

Conductor Count:	7
------------------	---

Insulation

Layer	Material	Nominal Wall Thickness
1	PP - Polypropylene	0.01 in
2	PE - Polyethylene	0.005 in

Color Chart

Number	Color
1	White over Blue
2	White over Orange
3	White over Green
4	White over Brown
5	White over Gray
6	White over Red
7	White over Yellow

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	1	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	28	7x36
Braid	2	Tinned Copper (TC)		65%			

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.19 in	0.019 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
63 Ohm/1000ft	7.2 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
12.5 pF/ft	23 pF/ft

Current

Max. Recommended Current [A]
0.9 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
150 V RMS

Mechanical Characteristics

Bulk Cable Weight:	22 lbs/1000ft
Min Bend Radius/Minor Axis:	2 in

Standards

Customer Reference Document:	IBM Part No. XX, YY Cable
NEC/(UL) Compliance:	CL2
Other Compliance:	RJ-45 compatible

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	150 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC
1540A 0081000	Gray	612825117643

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Patent # 5,220,130. Single conductors are dual insulated. Outer layer of insulation must be stripped off before attaching modular connectors.
--------	---

History

Update and Revision:	Revision Number: 0.258 Revision Date: 03-16-2021
----------------------	--

© 2021 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.