
Part Number : 354216802
Product Description : Tab Crimp Terminal 35421, AVS
Series Number : 35421
Status : Obsolete
Product Category : Crimp Terminals



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Obsolete

Downloaded from Arrow.com.

General

Status	Obsolete
Category	Crimp Terminals
Series	35421
Description	Tab Crimp Terminal 35421, AVS
Application	Wire-to-Wire
Product Name	N/A
UPC	800753943131

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.306/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	2.60mm max.
Wire Size (AWG)	16, 18
Wire Size mm^2	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	N/A
Max-Cycle	3
Max-Temp	260

Obsolete

Mates With / Use With

Mates with Part(s)

Description	Part Number
Tab Terminals	35420

Downloaded from Arrow.com.

This document was generated on Sep 17, 2026

Obsolete

Downloaded from Arrow.com.