

1242A Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1

**General Description:**

22 AWG solid bare copper conductors, conductors cabled, high density polyethylene insulation, PVC jacket.

Usage (Overall)

Suitable Applications: Station Wire, Telephone Wire

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	22	Solid	BC - Bare Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material
HDPE - High Density Polyethylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.140

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Green
2	Red
3	Yellow
4	Black

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
Bulk Cable Weight:	15 lbs/1000 ft.
Max. Recommended Pulling Tension:	32 lbs.
Min. Bend Radius/Minor Axis:	1.400 in.
Min. Bend/Installation:	1.400 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
EU Directive 2011/65/EU (RoHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004

1242A Multi-Conductor - Audio, Control and Instrumentation Cable

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Flame Test	
UL Flame Test:	UL1581 Vertical Tray
Plenum/Non-Plenum	
Plenum (Y/N):	No

Electrical Characteristics (Overall)

Nom. Inductance:
Inductance (µH/ft)
.17
Nom. Capacitance Conductor to Conductor:
Capacitance (pF/ft)
15
Nominal Velocity of Propagation:
VP (%)
66
Nominal Delay:
Delay (ns/ft)
1540
Nom. Conductor DC Resistance:
DCR @ 20°C (Ohm/1000 ft)
17.6
Nom. Attenuation:
Attenuation (dB/100 ft.)
0.53 @ 1MHz
Max. Operating Voltage - UL:
Voltage
300 V RMS (CM)
Max. Recommended Current:
Current
2.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1242A T35U1000	1,000 FT	16.000 LB	BEIGE, PALE FAWN		4 CNDR PE PVC CM BOX
1242A 008U1000	1,000 FT	16.000 LB	GRAY		4 CNDR PE PVC CM BOX

Revision Number: 1 Revision Date: 07-11-2012

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.