



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER						SIGNAL					POWER			
		E2	P8	P7	P6	P5	P4	5	4	3	2	1	P3	P2	P1	E1
51750-080-- NOTE: 3	D C B A		PA	PA	X	PD	PA	EX	EX	EX	EX	EX	PD	X	PD	



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
E	[N/A]	SIGNAL
PA	[1.07]	POWER
HA	[N/A]	HOLD-DOWN
PD	[2.34]	POWER
X	OMITTED	OMITTED

mat'l code				SEE NOTES		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date					COPY		www.fciconnect.com	
A	DG07-0213	JMG	05/22/07	linear		0.X ± 0.3		projection		title	
						0.XX ± 0.13				3P + 20S + 5P	
				angles		0.XXX ± 0.051				VERTICAL SOLDER RECEPT	
						0° ± 2°				product family PwrBlade	
				dr	JM GUO	05/22/07		scale		code	
				enr	RYAN YUAN	05/22/07				size	
				chr	GARY HSIEH	05/22/07				dwg no	
				appd	JOSEPH HSIA	05/22/07				51750-080	
sheet index	revision sheet	A	A	A	A					sheet 1 of 4	
		1	2	3	4					cage code	
										22526	




Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51750-080-
NOTE: 3



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ± 0.3	COPY		www.fciconnect.com	
A				linear	0.XX ± 0.13	projection		title	
				angles	0.XXX ± 0.051			3P + 20S + 5P	
				dr	0° ± 2°			VERTICAL SOLDER RECEPT	
				enr	JM GUO 05/22/07			product family PwrBlade	
				chr	RYAN YUAN 05/22/07			code	
				appd	GARY HSIEH 05/22/07			size	
					JOSEPH HSIA 05/22/07			dwg no	
sheet index	revision sheet					scale		A 51750-080	
								sheet	
								2 of 4	

cage code 22526

Pro/E


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER

51750-080-
NOTE: 3



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
A				linear	0.XX ±0.13	projection		title	
				angles	0.XXX ±0.051			3P + 20S + 5P	
				dr	0° ±2°			VERTICAL SOLDER RECEPT	
				enrg	JM GUO 05/22/07			product family PwrBlade	
				chr	RYAN YUAN 05/22/07			code	
				appd	GARY HSIEH 05/22/07			size	
					JOSEPH HSIA 05/22/07			dwg no	
sheet	revision							51750-080	
index	sheet							sheet	
								3 of 4	

Pro/E

cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51750-080-- NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- 2 HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. PLATING SPEC.
51750-080, 51750-080LF PLATING SPEC. WAS SHOWN IN THE PRINT OF 10064183.
- 4 MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.
- PCB NOTES:
7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 8 MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
- 9 $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER 0.03
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm .07$ HOLE.
- 10 "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
- 11 CONNECTOR KEEP-OUT ZONE.

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI www.fciconnect.com			
ltr	ecn no.	dr	date	linear	0.X ± 0.3		COPY		projection  MM scale 1:1	title 3P + 20S + 5P VERTICAL SOLDER RECEPT			
A					0.XX ± 0.13								
					angles	0.XXX ± 0.051							
				0° ± 2°									
				dr		JM GUO	05/22/07	product family		PwrBlade		code	
				enrg	RYAN YUAN	05/22/07	size		dwg no		213		
				chr	GARY HSIEH	05/22/07	A		51750-080		sheet		
				appd	JOSEPH HSIA	05/22/07					4 of 4		
sheet index		revision sheet											

cage code 22526