Part Number : 1202530042
Product Description : Contrinex Inductive Sensor, M12 Housing, 6mm Operating Distance, Quasi-embeddable, PNP, NO, 4-pin M12 Connector, 60mm Housing Length
Series Number : 120253
Status : Obsolete
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : DW-AS-503-M12



Documents and Resources

Specifications

1202530036-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Obsolete

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M12 Housing, 6mm Operating Distance, Quasi-embeddable, PNP, NO, 4-pin M12 Connector, 60mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130062126

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 800 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	60mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP (PPS)
Mounting Style	Quasi-embeddable
Net Weight	87.000/g
Operating Distance	6mm
Output	NO
Sensor Housing Size	M12
Temperature Range - Operating	-25° to +70°C

Obsolete

Downloaded from Arrow.com.

This document was generated on Sep 17, 2026

Obsolete

Downloaded from Arrow.com.