

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348033211

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

CTX64 Female Terminal, Tin, S-Grip, D-Wind, Left Payoff, SAE 22

Documents:	
Drawing (PDF)	Application Specification AS-560065-001-CH-001 (PDF)
Product Specification PS-502306-001-001 (PDF)	Application Specification AS-560065-001-FR-001 (PDF)
Application Specification AS-502306-002-001 (PDF)	Packaging Specification PK-31301-053-001 (PDF)
Application Specification AS-502306-002-CH-001 (PDF)	Brochure (PDF)
Application Specification AS-502306-002-FR-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-560065-001-001 (PDF)	

General	
Product Family	Crimp Terminals
Series	34803
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	CTX64
Taxonomy	Crimp Terminals
UPC	887191519272
Physical	
Gender	Female
Grip Code	S
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.114/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.10 to 1.65mm
Wire Size AWG	22
Wire Size mm²	0.22-0.35

Electrical	
Current - Maximum per Contact	See Receptacle Product Spec.
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-502306-002-001, AS-502306-002-CH-001, AS-502306-002-FR-001, AS-560065-001-001, AS-560065-001-CH-001, AS-560065-001-FR-001
Packaging Specification	PK-31301-053-001
Product Specification	PS-502306-001-001
Sales Drawing	SD-31301-053-001, SD-34803-002-001



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant

REACH SVHC
Not Contained per -
D(2022)9120-DC (17
Jan 2023)

Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image
ELV
RoHS Phthalates

Compliant
Not Contained

Search Parts in this Series

34803 Series

Use With

34729 2.54mm Pitch Stac64 Right Angle Receptacle

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global Description	Product #
Hand Crimp Tool for CTX64 Receptacle Terminal, 0.22, 0.30, 0.35mm² and 22 AWG	638193700
FineAdjust Applicator for CTX64 Mat Seal Receptacle Terminals, for Wire Process Use Only	639032600

This document was generated on 03/14/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION