


K11A39U2N, AL Universal Terminal, 2-Conductor, 2-Hole

By Burndy
Catalog # [K11A39U2N](#)

Aluminum Universal Terminal, 2 Hole, Two: 1/0 AWG (Str)-750 kcmil, 1/2" Stud, NEMA Stud Hole Spacing, 2 Screws, Al/Cu Rated, Tin Plated



Features

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- 1/2" diameter stud holes spaced 1-3/4" on center (NEMA-spacing)
- Range Taking conductor port

Application

Terminate multiple conductors onto equipment pads, panel boards, or switchgear

Specifications

Standards - Industry Standards Met	UL 486A-486B
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	Yes

Conductor

Conductor Size	1/0 AWG-750 KCMIL
Conductor - Copper Solid Size	<ul style="list-style-type: none"> • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Number Of Conductors	2
Conductor - Copper Solid Size Range	1/0 AWG-4/0 AWG
Conductor - AL Str Size	<ul style="list-style-type: none"> • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil

- 600 kcmil
- 636 kcmil
- 650 kcmil
- 700 kcmil
- 715 kcmil
- 750 kcmil

Conductor - AL Str Size Range
Conductor Type

- 1/0 AWG-750 kcmil
- AL C Str-Size
 - CU C Str-Size
 - CU C Solid-Size

Conductor Range
Conductor - Copper Str Size Range

- 750 Kcmil - #1/0 AWG
1/0 -750 kcmil

Conductor - Copper Str Size

- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil
- 300 kcmil
- 350 kcmil
- 400 kcmil
- 450 kcmil
- 500 kcmil
- 550 kcmil
- 600 kcmil
- 700 kcmil
- 750 kcmil

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	4
Connector Type	Stacked


Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Bolt Size fraction	3/8
Length	5.34 in
Dimension - Height inch	3.00 in
Thickness	0.50 in
Dimension - Height fraction	3 in
Package Weight	0.000 lb.
Dimension - Width mm	38 mm

Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	144 mm
Height	3 in
Width	1.5 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Screw Size inch	15/16
Dimension - Length Overall inch	5.69 in
Dimension - Stud Size fraction	3/8
Dimensions	5.34 in x 1.5 in x 3 in

General

Plated	Y
Material - Hardware	Aluminum



UPC	621945455986
Type	Bolted Lugs & Terminals
Material	Aluminum
Plating Type	Tin - Electro Plated
UPC 12 Digit	621945455986
UPC 14 Digit GTIN	00621945455986

Logistics

Minimum Pack Quantity	50
Pallet Quantity	1
Carton Quantity	18

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)

© 2026 Hubbell Incorporated. All rights reserved
BRDY-K11A39U2N-SPEC-EN | REV 5/2026