

DataShield Serial In-Line Surge Protector, DB25

MODEL NUMBER: **DB25-ALL**



Does your equipment have a DB25 connection? That connection is a potential inlet for damaging surges and line noise to affect your PC, printer or modem. Protect any DB25 serial connection with the DataShield™ DB25-ALL In-Line Surge Suppressor, and make sure your network is safe from power problems.

Description

Tripp Lite's DB25-ALL offers dataline surge suppression for any DB25 serial port, regardless of cable configurations. Connects and protects all 25 pins plus D shell chassis for universal protection of any DB25 application. User configurable for use with male or female captive DB25 port. Convenient DB25 input and output connects directly to the protected port, obtaining a ground outlet from the computer chassis. Surge suppression is handled with balanced arrays of high-speed avalanche diodes that divert excess energies created by electrostatic discharges away from network interface connections. Tripp Lite network surge suppressors reduce blown interface connections, garbled transmissions, system lock-ups and hard equipment failure by safely shunting dataline surges to ground.

SUPPRESSION: Reversible DB9 m/f jacks, protects pins 1-25 and chassis, 18V clamping

Features

- DB25 protects 25 pin serial connections for dataline surge suppression of data terminal, data communications equipments and PCs, printers, modems and more
- Reversible for use with male or female captive DB25 ports
- Offers protection on all 25 data lines, plus D shell chassis
- Surge suppression utilizing high speed avalanche diodes divert excess energies on the network to ground

Specifications

OVERVIEW	
UPC Code	037332010858
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC

Highlights

- Complete serial port (DB25) surge protection
- Protects against the effects of electrostatic discharge

Package Includes

- DB25-ALL dataline protector
- Instruction manual and warranty information

Recommended Electrical Service	120V, 230V
Input Plug Type	DB25
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(1) Network
Circuit Breaker (amps)	340
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Additional Dataline Protection	1-25 & Chassis
Telephone/DSL Protection	No
PHYSICAL	
Housing Color	Light Gray
Mounting Holes or Slots	No
Shipping Dimensions (hwd / in.)	5.00 x 3.00 x 2.00
Shipping Dimensions (hwd / cm)	12.70 x 7.62 x 5.08
Shipping Weight (lbs.)	0.16
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	0.720 x 2.250 x 2.780
Unit Weight (lbs.)	0.131
Unit Weight (kg)	0.06
FEATURES & SPECIFICATIONS	



1000 Eaton Boulevard
Cleveland, OH 44122
United States

Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.