



**Part Number :** [734151050](#)

**Product Description :** MCX Plug, Right-Angle, Crimp, RG-178, Die Cast Body, Nickel (Ni) Plated, 50 Ohms

**Series Number :** 73366

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents and Resources

### Drawings

[734151050\\_sd.pdf](#)

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 3; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Plug, Right-Angle, Crimp, RG-178, Die Cast Body, Nickel (Ni) Plated, 50 Ohms
Application	RF
Product Name	MCX
Style	Cable
Type	Microminiature
UPC	883906553470

### Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

### Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	1.228/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A

PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-178, RG-196

### **Solder Process Data**

Lead-Free Process Capability	N/A
------------------------------	-----

---

This document was generated on Jan 05, 2026