




Customer drawing



Dimensions					
Positions	A	B	D	E	F
9	30.81	24.99	16.33	11.08	19.20
15	39.20	33.30	24.70	19.39	27.70
25	53.05	47.04	38.40	33.24	41.10
37	69.40	63.50	54.80	49.86	57.30




50 Positions

REVISIONS			
SNV	ECN	DESCRIPTION	DATE
1	HK--	First Release Drawing	01/09/13
2	HK--	update Drawing	04/29/14
3	HK--	update Drawing	08/12/19

D-SUB TECHNICAL DATA

SHELL : SPCC, 100u" Tin over 50u" min nickel over 50u" min Copper
BODY : PBT, UL 94V-O, Color:Black.
CONTACTS : Copper Alloy.
Gold flash over 50u" min nickel on mating area.
100u" min tin over 50u" min nickel on solder area
REAR NUT: Copper Alloy, Nickel Plated.
ELECTRICAL : Voltage rating: 250 VAC(RMS) Max
Current rating: 3A
Withstanding Voltage >1000 VAC(RMS)
Insulation resistance >1000 M Ohms
Contact resistance 25 mOhms max.
MARKING : Amphenol...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE



DIMENSIONS OTHERWISE SPECIFIED			
TOLERANCES	U.S.	METRIC	APPROVAL
.X +/-	0.50	0.50	DATE
.XX +/-	0.30	0.30	09/12/19
.XXX +/-	0.20	0.20	CHECKED
ANGLES	5°	5°	09/12/19
SEE NOTES			
REMOVE SHARP EDGES			
DIMENSIONS			
TYPICAL			
ANGLE OF PROJECTION			
TITLE			
D-sub connector, solder cup series			
SIZE DRAWING NO.			
A4 L77SDXHXSS			
SCALE			
NONE			
SHEET 1 OF 1			