Specification Sheet

Part Number: 170-03006



Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.

Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.

Braided Sleeving, Expandable, Flame Retardant, 0.25" Dia, PET, Black, 200 ft/reel

Article Number	170-03006
Type	BSPFR140
Color	Black (BK)
Quantity Per	pack
Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification. This fire extinguishing braided sleeving is ideal for electronic and high tech applications because of its lightweight and durable qualities.
Short Description	Braided Sleeving, Expandable, Flame Retardant, 0.25" Dia, PET, Black, 200 ft/reel

Downloaded from Arrow.com.

Global Part Name	BSPFR140-PET-BK
Length L (Imperial)	200.0
Length L (Metric)	61.0
Bundle Diameter Min (Imperial)	0.13
Bundle Diameter Min (Metric)	3.2
Bundle Diameter Max (Imperial)	0.44
Bundle Diameter Max (Metric)	11.1
Diameter D (Imperial)	0.25
Diameter D (Metric)	6.4
Nominal Diameter (Imperial)	0.25
Nominal Diameter (Metric)	6.4
Material	Polyester (PET)
Material Shortcut	PET
Flammability	FMVSS 302 FAR 25 Mil-202 UL 224 VW-1
Halogen Free	Yes

Downloaded from Arrow.com.

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
BABA Compliant	YES
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 94 VW-1
UL Recognized (US)	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	60.96
Customs Number	5808100000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.