


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	Updated Graphics	07-31-26	LY



- NOTES:
- CABLE: UL20276
(30AWG*1PR+EAM)*2C+30AWG*1PR+24AWG*2C+AEB (AL) 65%
OUTER JACKET: BLACK, OD: 5.5 ± 0.2mm
 - CONNECTOR: USB 3.0 A TYPE MALE 9P
INSULATOR: BLUE
PIN G/F
NICKEL PLATED SHELL
 - CONNECTOR: USB 3.0 B TYPE MALE 9P
INSULATOR: BLUE
PIN G/F
NICKEL PLATED SHELL
 - PVC MOLDED: 45P BLACK COLOR
 - ELECTRICAL TEST:
<1>.100% OPEN SHORT & MISS WIRE TEST
<2>.INSULATION RESISTANCE: AC/DC 300V 10M ohm MIN.
<3>. CONDUCTOR RESISTANCE: 2 ohm MAX.
 - 1PC/POLYBAG W/LABEL

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. WCI DIVISION		
		Part Number: 3023015-02M		RoHS Compliant
0-1	0.15	Description: USB 3.0 A/M - USB 3.0 B/M		
1-6	0.20			
6-18	0.30	Drawn / Date	UNIT: mm	REV. B
18-50	0.50		Checked / Date	Approved / Date
50-120	0.70	R.Nuti 06-25-10	06-25-10	LY / 06-25-10
120-250	0.90			
250-500	1.20			

CONTROLLED