

DELPHI Connection Systems

Catalog

Customer Service

Comparison List (0)

Samples Request

Find by Feature

Browse by Category

Browse by Application

Share

12176388

Search

Enter part number or keyword

Search Results (1)

Search

Options

1 Result(s): [All] - 12176388

☐ Compare

12176388 - Metri-Pack 280 Series

☐ Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2

☐ Compare

Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2

Part # 12176388



Question about this product?

Attributes	Documents (2)
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	✔ 12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Part # :	12176388
Description :	Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2
Description :	Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2
Description :	Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2
Description :	✔ Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2
Description :	Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2
Description :	Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2
Description :	Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2
Description :	Metri-Pack 280 Series Female Sealed Silver Plating Tang Terminal, Cable Range 2.00 - 3.00 mm2

Status :	Active
Status :	Active
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	✓ 2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Blade size [mm] :	2.8
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	✓ M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Terminal Family :	M/P
Series :	280
Series :	280
Series :	280
Series :	✓ 280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280
Series :	280

Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Weight [g] :	1
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	✔ Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Plating :	Silver
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	✔ 2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Minimum Cable Diameter [mm] :	2.45
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	✔ 3.80
Maximum Cable Diameter [mm] :	3.80

Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Maximum Cable Diameter [mm] :	3.80
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	 2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Minimum Cable Core Cross Section [mm2] :	2.00
Maximum Cable Core Cross Section [mm2] :	3.00
Maximum Cable Core Cross Section [mm2] :	3.00
Maximum Cable Core Cross Section [mm2] :	3.00
Maximum Cable Core Cross Section [mm2] :	 3.00

Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
Voltage Drop :	Less than 3.0
RoHs compliant :	 Yes
ELV compliant :	 Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.



[Suppliers](#) | [Terms of Use](#) | [Privacy](#) | [Mexico Privacy Statement](#) | [Cookie Policy](#) | [Sitemap](#) | [European Safe Harbor](#) | [California Supply Chains Act](#)

© Delphi Automotive LLP. All rights reserved.