

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201140056](#)
Status: **Active**
Overview: [Brad Micro-Change \(M12\) Connectors](#)
Description: Micro-Change Molded Junction Box, Top Mount, 6 Ports, 2(OI) per port, LEDs for PNP sensors, with Field Wireable Home Run Connection



Series image - Reference only

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 1922-00000-00026-001 \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Passive Distribution Boxes
Series [120114](#)
Comments PNP SENSORS
IP Rating IP67
NEMA Rating NEMA 6
Overview [Brad Micro-Change \(M12\) Connectors](#)
Product Name Micro-Change (M12)
UPC 78678840175

Physical

Bus I/O Micro-Change (M12)
Cable Connector Orientation 90° Angle
Cable Length N/A
Home Run Cable Length N/A
Home Run Connector Terminal Strip
Home Run Interface Terminal Strip
Keyway Single
LED Indicator Yes
Material - Cable Jacket N/A
Material - Housing PBT
Material - Metal Copper Alloy
Material - Plating Mating Gold over Nickel
Orientation Top Mount
Poles 5
Poles (wired) 5
Ports 6
Temperature Range - Operating -20°C to +90°C
Wiring Configuration Dual I/O per Port

Electrical

Current - Maximum per Contact 12.0A per module, 4.0A per port
Functional Wiring Parallel
Voltage - Maximum 10-30V DC

Material Info

Engineering Number BTY603P-FBA

Reference - Drawing Numbers

Packaging Specification 1922-00000-00026-001
Sales Drawing SD-120114-066

EU ELV

Not Relevant

EU RoHS

Not Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[120114](#) Series

This document was generated on 12/11/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION