




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-010241	07-07-14	DM	DM
	A1	REVISED PER PCN E -20-004148	18MAR2020	AP	IG



5. SMALL NON-FILLS ARE ACCEPTABLE INSIDE OF PART, INCLUDING SUPPLIER MARKING.

4. SMALL MATERIAL EXTENSION IS ACCEPTABLE ON THIS END ALL AROUND. WALL THICKNESS ON THIS END MAY VARY.

3. THIS ACCESSORY PART IS PROVIDED WITHOUT TYPICAL TRANSPORTATION INDUSTRY PROCESS CONTROLS. NO VALIDATION TESTING HAS BEEN PERFORMED. CUSTOMER IS RESPONSIBLE FOR DETERMINING PRODUCT PERFORMANCE AND SUITABILITY FOR APPLICATION.

2. TEMPERATURE RATING: -29°C TO $+100^{\circ}\text{C}$ [-20°F TO $+212^{\circ}\text{F}$]

1. THIS PART IS USED ON DTM04-3P RECEPTACLES WITH ANY MODIFICATION THAT DOES NOT INCLUDE AN END CAP.

NOTES:

TE INTERNAL PN

DEUTSCH PN

DTM3P-BT

DTM3P-BT

© 2020 TE Connectivity. All Rights Reserved.

DIMENSIONS: MM [INCH]		DWN D. MEYER	07JUL2014	MATERIAL PVC		FINISH GRAY	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK B. MILLIGAN	07JUL2014	TE Connectivity			
		APVD D. MEYER	07JUL2014				
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.63[.025] 4 PLC ± ANGLES ±5°		PRODUCT SPEC		NAME BOOT, RECEPTACLE, 3PIN DTM SERIES	
APPLICATION SPEC							
				SIZE A 4	CAGE CODE 00779	DRAWING NO C-DTM3P-BT	RESTRICTED TO -
		WEIGHT 5.00 g					
CUSTOMER DRAWING				SCALE 5:4		SHEET 1 OF 1	
				REV A1			