
Your Expert Partner for **Human Machine Interfaces**

Actuator

704.064.2



https://www.eao.com/component/704.064.2/en/ac...

Downloaded from Arrow.com.

Your product:



704.064.2
Actuator

FRONT

Front dimension:	Ø 37 mm
Front form:	Round

MOUNTING

Design:	Raised
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens colour:	Red
Lens material:	Plastic
Lens illumination:	Non illuminated
Lens shape:	Mushroom-head
Lens optics:	opaque

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the “Standards for low-voltage switching devices” DIN EN 60947-1

MECHANICAL CHARACTERISTICS

Switching action:	Maintained
Release type:	Twist to unlock
Mechanical lifetime:	≤50 000 cycles of operation
Operating force:	8 N

Downloaded from Arrow.com.

Operating Travel:	ca. 5.8 mm ± 0.2 mm
Weight:	0.048 kg

AMBIENT CONDITION

IP Protection:	IP65 front side
Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C

CERTIFICATE


REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER


Short Description:	Actuator, Ø 37 mm, Mushroom-head, Non illuminated, Red, Plastic, opaque, Round, Maintained, Twist to unlock
Housing colour:	Yellow
Housing material:	Plastic
Marking:	Arrows
Product attributes:	Twist to unlock clockwise
Hints:	Shaft yellow
max. number of switching elements:	2
Wiring diagrams:	

Mounting cut-outs:

Downloaded from Arrow.com.



Dimension drawings:



A = Screw terminal

Downloaded from Arrow.com.