

Part Number : [2171750001](#)

Product Description : Universal Serial Bus (USB)
Shielded I/O Receptacle, Type C, Right-Angle, Surface
Mount, Top Mount, 6 Circuits, Gold (Au) Plating

Series Number : 217175

Status : Active

Product Category : I/O Connectors



Documents and Resources

Drawings

[2171750001_sd.pdf](#)

[2171750001-PK1.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2171750001-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	217175
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Surface Mount, Top Mount, 6 Circuits, Gold (Au) Plating
Application	Wire-to-Board
Component Type	Receptacle
Product Name	USB
Standard	USB 2.0
Type	C
UPC	195842116818

Electrical

Current - Maximum per Contact	1.25A
Grounding to Panel	None
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	30V AC/DC

Physical

Circuits (Loaded)	6
Circuits (maximum)	6

Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	Nylon
Mounting Style	Top-Mount
Net Weight	0.377/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.025µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

Mates With / Use With

Mates with Part(s)

Description	Part Number
USB Shielded I/O Type C Plugs	<u>105444</u>

This document was generated on Jul 07, 2026