

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-R7216 - P5

CATALOG LISTING
BZ-R7216 - P5
PAGE 1 OF 1

M

ISSUE
8

REPLACES

RELEASE NO. PR-4993

CHECK

REVISIONS

A	CO-39965	JJS	1 MAY 78
B	CO-44131	RJW	18 MAY 78
C	CO-73267-G	JAT	20 OCT 93
D	CO-75367B	KDR	3 MAR 94
E	CO-77863	GJW	1 MAY 96
F	CO93346	DLT	18 AUG 98
G	203225	CSL	7 JUN 01

CHECK

14 MAY 75

14 MAY 75

14 MAY 75

14 MAY 75

14 MAY 75

14 MAY 75

14 MAY 75

14 MAY 75


3X 8-32 UNC (.219) BINDING
HEAD COMBINATION TERMINAL
SCREW AND CUPWASHER

NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS
2 - CONTACT MATERIAL - GOLD ALLOY

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - - 7-9 OZ

RELEASE FORCE - - - - - 4 OZ MIN

DIFFERENTIAL TRAVEL - .00015-.00035

OVERTRAVEL - - - - - .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

-L22

-L288

-L299

-L307

1A 125 VAC



1A 250 V ~ T85 25E3

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

NO PLACES	DESIGN	TOL.	DESIGN	TOL.
	mm	mm/in	in	mm/in
ONE PLACE	X	1/64	X	0.015
TWO PLACES	X,X	0.0015	X,X	0.0015
THREE PLACES	X,XX	0.0005	X,XX	0.0005
ANGLES				

DESIGN UNITS ☐ SI METRIC

US CUSTOMARY ☒

WEIGHT .075 LB

FO-52848-A

DRAWN

