



Product: [7702NH](#)

LonWorks, 2PR #22 Sol BC, PO ins, Unsh, LSNH Jkt, 300V, Dca

Product Description

LonWorks, 2 Pair AWG 22 Bare Copper - Solid, Polyolefin (PO, PE, PP) insulation, Unshielded shielding, LSZH / FRNC jacket , 300V, CPR Dca

Technical Specifications

Product Overview

Suitable Applications:	LonWorks, instrumentation, Low capacitance
------------------------	--

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	Solid	BC - Bare Copper	0.64 mm	2
Conductor Count:			4	
Total Number of Pairs:			2	

Insulation			
Material	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness
PE - Polyethylene	1.12 mm	0.05 mm	0.23 mm

Color Chart	
Number	Color
Pair 1	White/Blue & Blue/White
Pair 2	Orange/White & White/Orange

Table Notes:	Ring marking applied
--------------	----------------------

Outer Shield

Material
No Shield

Outer Jacket			
Material	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	5.2 mm	0.4 mm	0.5 mm

Construction and Dimensions

Cabling	
Description	2 pairs twisted to cable core

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	55 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor
46 pF/m

Impedance

Frequency [MHz]	Nominal Characteristic Impedance
1 - 20	100 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss	Nom. NEXT [dB]
0.772 MHz	1.3 dB/100m	
1 MHz	1.5 dB/100m	59 dB
4 MHz	3.1 dB/100m	50 dB
10 MHz	4.9 dB/100m	44 dB
16 MHz	6.3 dB/100m	41 dB
20 MHz	6.9 dB/100m	40 dB

Current

Element	Max. Recommended Current [A]
Conductor(s)	2.5 Amps per Conductor

Voltage

Voltage Rating [V]
300 V

Temperature Range

Operating Temperature Range:	-15°C To +80°C
------------------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	31.2 kg/km
Max. Pull Tension:	50 N
Min. Bend Radius During Installation:	80 mm

Standards

CPR Euroclass:	Dca-s1,d1,a1
----------------	--------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Dca
----------------------	------------------------

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2, IEC 60332-3-24
IEC 60754-1 - Halogen Amount:	Zero

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
7702NH.00305	White	Reel	305 m	8719605013439
7702NH.00U305	White	UnReel	305 m	8719605013446

History

Update and Revision:	Revision Number: 0.233 Revision Date: 12-19-2022
----------------------	--

© 2023 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.