

# Mustang-V100-MX8



## Feature

- Half-Height, Half-Length, Single-slot compact size
- Low power consumption ,approximate 25W
- Supported OpenVINO™ toolkit, AI edge computing ready device
- Eight Intel® Movidius™ Myriad™ X VPU can execute multiple topologies simultaneously.



## Specifications

Model Name	Mustang-V100-MX8
Main Chip	Eight Intel® Movidius™ Myriad™ X MA2485 VPU
Operating Systems	Ubuntu 18.04.x 16.04.x LTS 64bit, CentOS 7.4 64bit, Windows® 10 64bit
Dataplane Interface	PCI Express x4 Compliant with PCI Express Specification V2.0
Power Consumption	Approximate 25W
Operating Temperature	-20°C~60°C
Cooling	Active fan
Dimensions Standard	Half-Height, Half-Length, Single-slot PCIe
Operating Humidity	5% ~ 90%
Power Connector	*Preserved PCIe 6-pin 12V external power
Dip Switch/LED indicator	Identify card number
Support Topology	AlexNet, GoogleNetV1/V2, MobileNet SSD, MobileNetV1/V2, MTCNN, Squeezenet1.0/1.1, Tiny Yolo V1 & V2, Yolo V2, ResNet-18/50/101 * For more topologies support information please refer to Intel® OpenVINO™ Toolkit official website. [Supported Models] <a href="https://docs.openvino toolkit.org/latest/_docs_IE_DG_Introduction.html#SupportedFW">https://docs.openvino toolkit.org/latest/_docs_IE_DG_Introduction.html#SupportedFW</a> [Supported Framework Layers] <a href="https://docs.openvino toolkit.org/latest/_docs_MO_DG_prepare_model_Supported_Frameworks_Layers.html">https://docs.openvino toolkit.org/latest/_docs_MO_DG_prepare_model_Supported_Frameworks_Layers.html</a>

\*TANK AIoT dev. kit PCIe slot provides 75W power, this feature is preserved for user in case of different system configuration.


Warning: DO NOT install the Mustang-V100-MX8 into the TANK AIoT Dev. Kit before shipment. It is recommended to ship them with their original boxes to prevent the Mustang-V100-MX8 from being damaged.

## Ordering Information

Part No.	Description
Mustang-V100-MX8-R11	Computing Accelerator Card with 8 x Movidius Myriad X MA2485 VPU, PCIe Gen2 x4 interface, RoHS

## Packing List

- 1 X Full height bracket
- 1 x External power cable
- 1 x QIG



### Mustang-V100-MX8 Block Diagram

- 8 Intel® Movidius™ Myriad™ X VPU delivering up to 8 TOPs of dedicated networks compute
- Interface: PCIe Gen2 x 4
- Form Factor: Standard Half-Height, Half-Length, Single-slot
- Cooling: Active fan.
- Operation Temperature: -20°C~60°C
- Operation Humidity : 5% to 90% relative humidity
- Power Consumption: Approximate 25W
- Power Connector: \*Preserved PCIe 6-pin 12V external power
- DIP Switch/LED Indicator: Identify card number.

### Mustang-V100-MX8 Dimensions (Unit: mm)

